

**INSTRUCCIONES DE TRABAJO**

Versión nº: 2 Fecha de revisión: Septiembre 2011

IDT-605: Fichas técnicas de producto

**TECHNICAL DATA****LOOP 001****Construction characteristics**

Basic construction  
 Base material  
 Standard binder backing

Width : < 50 mm  
 ≥ 50 mm  
 ≥ 100 mm

Overall thickness

Weight

**Usage characteristics**

Peel Strength with Hook std \*

Shear Strength with Hook std \*

Cycle life \*

Breaking Strength \*

Shrinkage after washing ( 3 x 60°C ) \*

Colourfastness to washing UNE-EN ISO 105-C10  
 Colourfastness to dry cleaning ISO 105 sec/DO1  
 Colourfastness to rubbing ISO 105 sec/X12  
 Colourfastness to water ISO 105 sec/EO1  
 Colourfastness to sea water ISO 105 sec/EO2  
 Colourfastness to light ISO 105 sec/BO2

Colourfastness to perspiration ISO 105 sec/EO4

\* Internal norm of VESA

Woven  
 Polyamide  
 Synthetic resin

Nominal ± 1 mm  
 Nominal ± 1.5 mm  
 Nominal ± 2 mm

2.35 ± 0.25 mm

300 g/m<sup>2</sup> ± 10 %

Average 2.0 N/cm  
 Minimum 1.3 N/cm

Average 10.3 N/cm<sup>2</sup>  
 Minimum 7.3 N/cm<sup>2</sup>

50 % loss after 10000 cycles

Minimum 210 N/cm

Maximum 4 %

4 minimum  
 4 minimum  
 4 minimum  
 4 minimum  
 4 minimum  
 5 minimum (dark colours)  
 4 minimum (white and light colours)  
 3 minimum (fluor colours)  
 4 minimum

The information included in this Technical Sheet is based on reliable tests and trials. Average value as a reference only, not a nominal specification. Given the diversity of uses of our products we advise our customers to assure themselves that the product meets the requirements of their application. The responsibility for the application and use of the product remains with the customer.

Elaborado: J.C. Lima

Revisado: E. Ducet

Autorizado: J. Jacobs

Fecha: 27.09.11

ANEXO: IDT – 605-B

FTP 200 Versión 4