



Main

Range	Odace
Product or component type	Cable outlet
Device presentation	Mechanism with fixing frame
Product specific application	Exit wire for electrical heating
Type of packing	Paint cover

Complementary

Device mounting	Flush
Rated current	16 A
Fixing mode	By claws By screws
Colour tint	White (RAL 9003)
Surface finish	Glossy
Connections - terminals	Screw terminals
Number of loop terminals	2
Shape of screw head	Pozidriv No 1
Clamping connection capacity	1 x 1.5...1 x 2.5 mm ² for rigid cable(s) 1 x 1.5...1 x 2.5 mm ² for flexible cable(s) 1 x 1.5...1 x 2.5 mm ² for stranded cable(s)
Cable outer diameter	6...12 mm
Wire stripping length	12 mm
Material	Thermoplastic ABS-UV stabilised: centre plate PBT (polybutylene terephthalate) GF30: support frame
Height	71 mm
Width	71 mm
Depth	54 mm
Embedding depth	26.7 mm
Net weight	0.036 kg
Resistance to chemical agents	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Environment

Ambient air temperature for storage	-5...50 °C
Ambient air temperature for operation	5...35 °C
Standards	UTE C 61-392 EN 60669-1
Product certifications	LCIE: NF 603415A
IK degree of protection	IK04
IP degree of protection	IP2XC

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Compliant EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
Minimum percentage of recycled plastic content	13