

# Product information

## 18V IMPACT DRIVER LI-ION



### DTD129Z

Electric Brake	1
Voltage	18 v
Max Fastening Torque	160 Nm
No Load Speed	0 - 2500 rpm
Battery Type	Lithium-ion
Vibration: Fastening Bolt	15 m/sec <sup>2</sup>
Vibration K factor	1.5 m/sec <sup>2</sup>
Body only machine	1
Net weight	1.5 kg
Variable Speed Control	Trigger
Driving Shank	6.35mm (1/4") Hex
Machine Screw	M4-M8
Impacts per Minute	0-3200 ipm



- LED Job light with pre-glow function.
- BLDC motor specially designed to provide, above all, more work amount on a single full battery charge.
- Fully Compatible with 18V 4.0Ah Battery with 36 minute charge time.
- Energy production is more efficient than brushed DC motor because of no friction loss caused by brushes, enabling lower amperage for reduced heat production and increased work amount on a single full battery charge.

Details correct as of: 3-6-2014

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

[www.makita.com](http://www.makita.com)