



Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: **Receptacle**
Connector & Housing Type: **Receptacle**
Number of Positions: **3**
Terminal Orientation: **Straight**
UL Flammability Rating: **UL 94V-2**

Features

Product Type Features

Sealable	No
Connector & Housing Type	Receptacle

Configuration Features

Number of Positions	3
---------------------	---

Body Features

Primary Product Color	Black
-----------------------	-------

Contact Features

Terminal Type	Receptacle
Terminal Orientation	Straight
Contact Mating Retention	Without

Mechanical Attachment

Mating Alignment	With
Connector Mounting Type	Cable Mount (Free-Hanging)



Housing Features

Housing Material	Nylon
------------------	-------

Dimensions

Product Length	28 mm[1.1 in]
----------------	---------------

Usage Conditions

Operating Temperature Range	-40 – 105 °C[-40 – 221 °F]
-----------------------------	----------------------------

Industry Standards

UL Flammability Rating	UL 94V-2
------------------------	----------

Packaging Features

Packaging Quantity	1
Packaging Method	Carton

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

 TE Part # 521381-1 FF 187 REC HSG 6P NYLON BLACK	 TE Part # 1-480281-0 FF 250 REC HSG 6P NYLON BLACK	 TE Part # 880107-2 HOUSING 8P .110 FASTON	 TE Part # 150653-1 FF 312 REC HSG 3P NYLON BLACK
 TE Part # 626213-1 FASTIN-ON 0.312 FLAG REC NYLON 6.6	 TE Part # 925176-5 FF 312 3P HOUSING REC POLYAMID 6.6 BLACK	 TE Part # 140885-5 FF 250 REC HSG 6P NYLON BLACK	 TE Part # 1-480252-0 FF 187 REC HSG 3P NYLON NAT
 TE Part # 626213-2 3 CIR FASTIN-ON RECP HSG PRETO	 TE Part # 925306-3 FF 312 REC HSG 3P NYLON BLACK	 TE Part # 171090-1 FF 250 REC HSG 14P NYLON	 TE Part # 1534690-1 FASTIN FASTON HOUSING 4POS 2,8 MM
 TE Part # 880137-2 3W FASTIN-ON REC. HSG	 TE Part # 480054-4 FF 250 REC HSG 1P NYLON BLACK	 TE Part # 480115-3 FF 250 REC HSG 2P NYLON BLACK	

Also in the Series | FASTIN-FASTON 312

 Crimp Terminal Housings(11)	 Quick Disconnects(9)
--	--



Customers Also Bought

TE Part #1060-16-0144-PS
PIN, SF, SIZE 16, 14-18, AU/SN, 100 PC

TE Part #2178473-3
3POS UMNL PLUG HSG GW

TE Part #36807
TERMINAL,SOLIS R 6 3/8

TE Part #770428-1
09P .062 COMM P&S PLUG

TE Part #2304643-4
60POS,AMP MCP 2.8,REC HSG ASSY, SLD

TE Part #HD36-24-29PE
PLG, 29P, AL, E, 12/16/20, P

TE Part #2238104-1
250 PL MKII REC. 16-14AWG NPST

TE Part #4-456406-7
CRIMPER, WIRE .090 F

TE Part #4-456134-6
CRIMPER, INSULATION "F"(.180")

TE Part #1744417-5
5 POS EP 2.5 HSG, GLOW WIRE

Documents

Product Drawings

FF 312 REC HSG 3P NYLON BLACK

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_480100-1_AH_c-480100-1-ah.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_480100-1_AH_c-480100-1-ah.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_480100-1_AH_c-480100-1-ah.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.



Datasheets & Catalog Pages

FASTIN_FASTON_Product_Line

English

White Paper: Nylon Discoloration

English

Product Specifications

Application Specification

English