

# HC-DD108-I-CT-F - Contact insert



1584130

<https://www.phoenixcontact.com/gb/products/1584130>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Contact insert, number of positions: 108+PE, size: B24, number of connections per position: 1, Socket, Crimp connection, 250 V, 10 A, 0.14 mm<sup>2</sup> ... 2.5 mm<sup>2</sup>, application: Signal

## Your advantages

- Can be used in rail vehicles, satisfy DIN EN 45545-2 with requirement sets R22, R23, and R24 in hazard levels HL1, HL2, and HL3.
- Shock and vibration-resistant in accordance with DIN EN 61373

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1584130       |
| Packing unit                         | 1 pc          |
| Minimum order quantity               | 1 pc          |
| Sales key                            | AF7ABF        |
| Product key                          | AF7ABF        |
| GTIN                                 | 4046356133449 |
| Weight per piece (including packing) | 79.32 g       |
| Weight per piece (excluding packing) | 79 g          |
| Customs tariff number                | 85389099      |
| Country of origin                    | CN            |

# HC-DD108-I-CT-F - Contact insert

1584130

<https://www.phoenixcontact.com/gb/products/1584130>



## Technical data

### Mounting

|               |                                                                                           |
|---------------|-------------------------------------------------------------------------------------------|
| Assembly note | To ensure correct use, installation in housing with IP54 protection or better is required |
|---------------|-------------------------------------------------------------------------------------------|


### Product properties

|                                    |                                              |
|------------------------------------|----------------------------------------------|
| Product type                       | Contact insert with a fixed no. of positions |
| Series                             | HC-DD                                        |
| Application                        | Signal                                       |
| Type                               | B24                                          |
|                                    | B48                                          |
| Number of positions                | 108                                          |
| Connection profile                 | 108+PE                                       |
| Contact numbering                  | 1 - 108                                      |
| Number of connections per position | 1                                            |
| Contact material type              | turned                                       |
|                                    | rolled                                       |

### Insulation characteristics

|                      |     |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution  | 3   |

### Dimensions

|                                 |                                                                                      |
|---------------------------------|--------------------------------------------------------------------------------------|
| Dimensional drawing             |  |
| Width                           | 34 mm                                                                                |
| Height                          | 34.5 mm                                                                              |
| Length                          | 111 mm                                                                               |
| Drill hole distance, horizontal | 104 mm                                                                               |
| Drill hole distance, vertical   | 27 mm                                                                                |

### Mechanical characteristics

|                        |        |
|------------------------|--------|
| Minimum housing height | 72 mm  |
| Contact diameter       | 1.6 mm |

### Connection data

#### Connection technology

|                                    |                  |
|------------------------------------|------------------|
| Connection technology              | Crimp connection |
| Number of connections per position | 1                |
| Connection in acc. with standard   | IEC / EN         |

# HC-DD108-I-CT-F - Contact insert



1584130

<https://www.phoenixcontact.com/gb/products/1584130>

## Conductor connection

|                                         |                                                                          |
|-----------------------------------------|--------------------------------------------------------------------------|
| Conductor cross-section                 | 0.14 mm <sup>2</sup> ... 2.5 mm <sup>2</sup>                             |
| Connection cross section AWG            | 26 ... 14                                                                |
| Tightening torque                       | 0.8 Nm ... 1.2 Nm (PE connection)                                        |
|                                         | 0.5 Nm ... 0.8 Nm (Mounting screws for mounting in the HEAVYCON housing) |
| Stripping length of the individual wire | 8 mm (0.14 mm <sup>2</sup> ... 1.5 mm <sup>2</sup> )                     |
|                                         | 6 mm (2.5 mm <sup>2</sup> )                                              |

## Electrical properties

|                       |                |
|-----------------------|----------------|
| Rated voltage (III/3) | 250 V          |
| Rated surge voltage   | 4 kV           |
| Rated current         | 10 A           |
| SCCR                  | 5 kA (UL 2237) |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 500 |
|-----------------------------|-------|

## Material specifications

|                                        |                       |
|----------------------------------------|-----------------------|
| Flammability rating according to UL 94 | V0                    |
| Contact material                       | Copper alloy          |
| Contact surface material               | Ag (alternatively Au) |
| Contact carrier material               | PC                    |
| Standards/regulations                  | PC                    |

## Environmental and real-life conditions

### Ambient conditions

|                                 |                                                      |
|---------------------------------|------------------------------------------------------|
| Ambient temperature (operation) | -40 °C ... 125 °C (including heating up of contacts) |
|---------------------------------|------------------------------------------------------|

## Standards and regulations

|                                        |                            |
|----------------------------------------|----------------------------|
| Constructional and testing regulations | DIN VDE 0627/86            |
|                                        | DIN VDE 0110/02.79         |
|                                        | DIN VDE 0110-1/04.97       |
|                                        | IEC 60664-1, DIN IEC 60512 |
|                                        | IEC 60352                  |
| Tests                                  | DIN VDE 0627/86            |
|                                        | DIN VDE 0110/02.79         |
|                                        | DIN VDE 0110-1/04.97       |
|                                        | IEC 60664-1, DIN IEC 60512 |
|                                        | IEC 60352                  |

### Testing

# HC-DD108-I-CT-F - Contact insert



1584130

<https://www.phoenixcontact.com/gb/products/1584130>

| Standards/regulations | PC: Fire protection in rail vehicles - requirement sets R22, R23, and R24 acc. to DIN EN 45545-2 (Risk level HL1 - HL3) |
|-----------------------|-------------------------------------------------------------------------------------------------------------------------|
|-----------------------|-------------------------------------------------------------------------------------------------------------------------|

# HC-DD108-I-CT-F - Contact insert


1584130

<https://www.phoenixcontact.com/gb/products/1584130>




## Drawings

Dimensional drawing



Female insert

Dimensional drawing



Mounting cutout when used without housing


# HC-DD108-I-CT-F - Contact insert

1584130

<https://www.phoenixcontact.com/gb/products/1584130>



Schematic diagram



Connector pin assignment, connection side


# HC-DD108-I-CT-F - Contact insert

1584130

<https://www.phoenixcontact.com/gb/products/1584130>




Diagram



Derating diagram turned contacts

Diagram



Derating diagram rolled contacts

# HC-DD108-I-CT-F - Contact insert



1584130

<https://www.phoenixcontact.com/gb/products/1584130>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1584130>

### DNV

Approval ID: TAE000037S



### CSA

Approval ID: 013631\_6233\_01

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 250 V                 | 7 A                   | 26 - 14           | -                           |



### cUL Recognized

Approval ID: E118976

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 250 V                 | 7 A                   | - 14              | -                           |



### UL Recognized

Approval ID: E118976

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 250 V                 | 10 A                  | - 14              | -                           |



### cULus Recognized

Approval ID: E468743

|       | Nominal voltage $U_N$ | Nominal current $I_N$ | Cross section AWG | Cross section $\text{mm}^2$ |
|-------|-----------------------|-----------------------|-------------------|-----------------------------|
| keine |                       |                       |                   |                             |
|       | 250 V                 | 7 A                   | - 14              | -                           |

# HC-DD108-I-CT-F - Contact insert

1584130

<https://www.phoenixcontact.com/gb/products/1584130>



## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-13.0 | 27440205 |
| ECLASS-15.0 | 27440205 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC000438 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121500 |
|-------------|----------|

# HC-DD108-I-CT-F - Contact insert

1584130

<https://www.phoenixcontact.com/gb/products/1584130>



## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)