



Residual current circuit breaker (RCCB), 80A, 4p, 300mA, type A



Part no. PXF-80/4/03-A
Catalog No. 102879

Similar to illustration

Delivery program

Basic function			Residual current circuit-breakers
Number of poles			4 pole
Application			Switchgear for residential and commercial applications
Rated current	I_n	A	80
Rated short-circuit strength	I_{cn}	kA	10
Rated fault current	$I_{\Delta N}$	A	0.3
Type			Type A
Tripping		s...	non-delayed
Product range			PXF
Sensitivity			Pulse-current sensitive
Impulse withstand current			Partly surge-proof 250 A

Technical data

Electrical

Standards			IEC/EN 61008
Rated operational voltage	U_e	V	
	U_e	V AC	
Rated operating voltage	U_e	V AC	230/400
Rated frequency	f	Hz	50
Limit values of the operating voltage			
Test circuit		V AC	184 - 440
Sensitivity			Pulse-current sensitive
Rated insulation voltage	U_i	V	440
Rated impulse withstand voltage	U_{imp}	kV	4
Rated short-circuit strength	I_{cn}	kA	10
Rated making and breaking capacity / Rated residual making and breaking capacity	$I_m / I_{\Delta m}$	A	800
lifespan			
Electrical	Operations		≥ 4000
Mechanical	Operations		≥ 20000

References

Auxiliary switch for subsequent installation			Z-HK 248432
Tripping signal contact for subsequent installation			Z-NHK 248434
Remote control and automatic switching device			Z-FW/LP 248296
Compact enclosure			KLV-TC-4 276241
Switching interlock			IS/SPE-1TE 101911
Sealing cover set			Z-RC/AK-4MU 101062

Mechanical

Standard front dimension		mm	45
Device height		mm	80
Built-in width		mm	70 (4TE)
Mounting			Quick attachment with 2 latch positions for DIN-rail IEC/EN 60715
Degree of Protection			IP40, IP54 (with moisture-proof enclosure)
Terminals top and bottom			Open mouthed/lift terminals
Terminal protection			DGUV VS3, EN 50274
Terminal cross-section			

Solid	mm ²	1.5 - 35
Stranded	mm ²	2 x 16
Thickness of busbar material	mm	0.8 - 2
Permissible storage and transport temperatures	°C	-35 - +60
Climatic proofing		25-55°C/90-95% relative humidity according to IEC 60068-2

Design verification as per IEC/EN 61439

Technical data for design verification			
Rated operational current for specified heat dissipation	I _n	A	80
Heat dissipation per pole, current-dependent	P _{vid}	W	0
Equipment heat dissipation, current-dependent	P _{vid}	W	11.4
Static heat dissipation, non-current-dependent	P _{vs}	W	0
Heat dissipation capacity	P _{diss}	W	0
Operating ambient temperature min.		°C	-25
Operating ambient temperature max.		°C	60
			Starting at 40 °C, the max. permissible continuous current decreases by 1.2% for every 1 °C
IEC/EN 61439 design verification			
10.2 Strength of materials and parts			
10.2.2 Corrosion resistance			
10.2.2.1 Verification of thermal stability of enclosures			
10.2.2.2 Verification of resistance of insulating materials to normal heat			
10.2.2.3 Verification of resistance of insulating materials to abnormal heat and fire due to internal electric effects			
10.2.4 Resistance to ultra-violet (UV) radiation			
10.2.5 Lifting			
10.2.6 Mechanical impact			
10.2.7 Inscriptions			
10.3 Degree of protection of ASSEMBLIES			
10.4 Clearances and creepage distances			
10.5 Protection against electric shock			
10.6 Incorporation of switching devices and components			
10.7 Internal electrical circuits and connections			
10.8 Connections for external conductors			
10.9 Insulation properties			
10.9.2 Power-frequency electric strength			
10.9.3 Impulse withstand voltage			
10.9.4 Testing of enclosures made of insulating material			
10.10 Temperature rise			
10.11 Short-circuit rating			
10.12 Electromagnetic compatibility			
10.13 Mechanical function			

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Residual current circuit breaker (RCCB) (EC000003)			
Electric engineering, automation, process control engineering / Electrical installation, device / Residual current protection system / Residual current circuit breaker (RCCB) (ecl@ss10.0.1-27-14-22-01 [AAB906014])			
Number of poles			4
Rated voltage	V		400
Rated current	A		80
Rated fault current	mA		300
Rated insulation voltage U _i	V		440
Rated impulse withstand voltage U _{imp}	kV		4

Mounting method			DIN rail
Leakage current type			A
Selective protection			No
Short-time delayed tripping			No
Short-circuit breaking capacity (I _{cn})		kA	10
Surge current capacity		kA	0.25
Frequency			50 Hz
Additional equipment possible			Yes
With interlocking device			Yes
Degree of protection (IP)			IP20
Width in number of modular spacings			4
Built-in depth		mm	70.5
Ambient temperature during operating		°C	-25 - 40
Pollution degree			2
Connectable conductor cross section multi-wired		mm ²	1.5 - 16
Connectable conductor cross section solid-core		mm ²	1.5 - 35