




HIGH RESOLUTION COLOR BULLET CAMERA

7769383

► CAUTION

- Do not open or strike this equipment. Sensitive electronics inside are vulnerable to excessive shock.
 - Do not install the equipment near any naked flames or heat sources. Excessive heat could damage this unit.
 - Do not cover cloth or to install this unit in poorly ventilated places. This may lead to overheating.
 - Do not continue to operate if there appears to be fault.
- If the unit ceases to function, contact qualified service personnel for help.
- Do not touch the power connection with wet hands. Risk of short circuit or electric shock.
 - Do not damage the power cord or leave it under pressure. Risk of fire or shock circuit.



FEATURE

1/3" COLOR SONY EXVIEW II CCD HIGH RESOLUTION (19Φ)

- 700TV Line (Color)
- Day & Night
- Minimum Illumination : 0.005 Lux (F:1.2)
- Auto White Balance
- Automatic Gain Control
- Dimension(mm) : 19(Φ) × 71
- Power Source : DC12V (6.5V ~ 28V)
- Standard 500mm, BNC/DC Jack
- Waterproof

SPECIFICATION	
Image Device	1/3" Color SONY SUPER HAD II CCD(960H)
Picture Elements	1020(H)×508(V) 1020(H)×596(V)
Sync System	Internal Synchronization
Horizontal Resolution	700 TV Line (Color) 750 TV Line (B/W Mode)
Video Output	1Vp-p 75Ω Composite
S/N Ratio	More Than 52dB (AGC Off)
Gamma Characteristic	0.45
Gain Control	Auto
White Balance	Auto 1800°K ~ 10500°K
Electronic Shutter	1/60~1/100,000sec (Auto) 1/50~1/100,000sec (Auto)
LENS	3.6mm Fixed Lens
Lens Option	6mm, 8mm, 12mm, 16mm or Pinhole lens
Smear Effect	0.005%
Minimum Illumination	0.005 Lux (F:1.2)
Power Consumption	DC12V (6.5V ~ 28V), 100mA
Operation Temperature	-10℃ ~ +50℃
Storage Temperature	-20℃ ~ +60℃
Weight	Approx 85g included bracket
Housing	ALUMINUM
Dimension(mm)	19Φ × 71
Cable(option)	Standard 500mm BNC/DC Jack