


3535-60

optibelt TB Taper-Bushings with metric bores



3D-View

To activate the interactive 3D view, you must trust this document (see hint on the top) in Adobe Acrobat and click on the question mark.



Zoom

Moves you toward or away from objects in the scene when you drag vertically. You can also zoom with the hand tool by holding down Shift as you drag.

Pan

Moves the model vertically and horizontally only. You can also pan with the hand tool: Ctrl-drag.

Rotate

Turns 3D objects around relative to the screen. How the objects move depends on the starting view, where you start dragging and the direction in which you drag.



3535-60

optibelt TB Taper-Bushings with metric bores



2D-View

ISO-View



3535-60



optibelt TB Taper-Bushings with metric bores



Technical Data

BEZ (Designation Sales)	3535-60
ANR (Part ID)	1659526
GTIN (Global Trade Item Number)	4014486253191
AUSFNR (Type ID)	2
D1 (Bushing Diameter large Conus / mm)	126.8
L (Bushing Length / mm)	89.0
DB (Bore Diameter / mm)	60
DBMAX (max. Bore Diameter / mm)	95
BT (ISO Bore Tolerance)	G7
B (Keyway Width / mm)	18
T1 (Keyway Depth / mm)	4.4
T2 (DB + T1)	DB+4,4
NT (ISO Keyway Tolerance)	JS9
NA (Keyway Dimensions)	acc. to DIN 6885 part 1
FN (Type with shallow Keyway)	No
GEWICHT (approx. Weight / kg)	5.23
MATERIAL (Material)	EN-GJL 200 - DIN EN 1561
OF (Surface Treatment)	Phosphated
QS (Quality Standard)	acc. to ISO 254
AMP (Screw Tightening Torque with Feather Key / Nm)	95
AM (Screw Tightening Torque without Feather Key / Nm)	112
UED (Max. Transmittable Torque with Feather Key* / Nm)	5060
ST (Screw Type)	Allan Head Screw 1/2" x 1 1/2" BSW
SA (Amount of Screws)	3
SW (Wrench Size / mm)	10 (Allan Head Wrench)

*without safety-factor and depending on the bore diameter



We reserve the right to make technical changes.

Shaft- $\varnothing$ $\leq$ 30 mm up to ISO-tolerance class h11, > 30 mm up to h9