






PRODUCT DATASHEET

Datasheet creation date: 2025/06/02 9:46 (UTC)



60BER19H

ROBUST Series Ultra High-Speed Angular Contact Ball Bearings



Parts Number

60BER19HTXV1VSUELP3

Boundary Dimensions

	BER: 25°		Bearing Type
d	60	mm	Bore diameter
D	85	mm	Outside diameter
B	13	mm	Width
BN	2.8	mm	
SN	7.5	mm	
SB	1.4	mm	
r(min.)	1	mm	Chamfer Dimension
r1(min.)	0.6	mm	Chamfer Dimension

Basic Load Ratings

Cr	17.6	kN	Basic Dynamic Load Rating
C0r	11.0	kN	Basic Static Load Rating

Speeds

Grease	22100	min-1	Limiting Speed
Oil (Oil-air)	34500	min-1	Limiting Speed

Dimensions

	25°		Contact Angle
a	23.4	mm	Effective Load Center

Abutment and Fillet Dimensions

da(min.)	66	mm	Diameter of Shaft Abutment
Da(max.)	79	mm	Diameter of Housing Abutment
Db(max.)	80	mm	Diameter of Housing Abutment
ra(max.)	1	mm	Radius of Shaft or Housing Fillet
rb(max.)	0.5	mm	Radius of Shaft or Housing Fillet

Performance

Pa	13.6	kN	Permissible Axial Load
----	------	----	------------------------



PRODUCT DATASHEET

Datasheet creation date: 2025/06/02 9:46 (UTC)



Table A		EL	L	M	H
	15°	6.5	6.0	5.0	4.5
	25°	2			
	30°	1.4			

Table B	DBD	DBB
Preload factor	1.36	2
Axial rigidity	1.48	2
Radial rigidity	1.54	2

Calculation of radial rigidity
Multiply axial rigidity by the appropriate factor in Table A.

Calculation of preload and axial rigidity for combined bearings
Multiply by the appropriate factor in Table B. For radial rigidity, multiply the value from Table A with the appropriate factor in Table B.

Preload,Rigidity(DB and DF arrangement)

	Preload	Axial Rigidity	Measured axial clearance
EL	49N	88N/μm	0μm
L	306N	164N/μm	-8μm
M	638N	215N/μm	-15μm

Additional information

1.1	g/brg	Recommended Grease Quantities
-----	-------	-------------------------------

Mass

0.170	kg	Mass(approx.)
-------	----	---------------