




**Part Number :** [754515001](#)

**Product Description :** Small Form-factor Pluggable (SFP) Stacked 2-by-6 Multi-Port Connector with 4 Lightpipes, with Press-fit PC Tails, 240 Circuits, Lead-Free

**Series Number :** 75451

**Status :** Active

**Product Category :** High-Speed I/O Connectors



---

## Documents & Resources

### Drawings

[754515001\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

### Specifications

[AS-75310-001-001.pdf](#)

[AS-76090-001-001.pdf](#)


[PK-75451-001-001.pdf](#)

[PS-75310-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

## Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	High-Speed I/O Connectors
Series	75451
Description	Small Form-factor Pluggable (SFP) Stacked 2-by-6 Multi-Port Connector with 4 Lightpipes, with Press-fit PC Tails, 240 Circuits, Lead-Free
Application	Module-to-Board
Comments	With 4 Lightpipes
Component Type	Receptacle
Product Name	SFP
Type	Pluggable
UPC	822350125994

### Agency

CSA	LR19980
UL	E29179

### Electrical

Current - Maximum per Contact	0.5A
-------------------------------	------

Data Rate	10.0 Gbps
Shielded	Yes
Shield Type	EMI Fingers
Voltage - Maximum	30V

## Physical

Circuits (Loaded)	240
Circuits (maximum)	240
Color - Resin	Black, Clear (Blue Tint)
Durability (mating cycles max)	200
Flammability	94V-0
Lock to Mating Part	Yes
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic, Polycarbonate
Net Weight	150.326/g
Orientation	Right Angle
Packaging Type	Tray
Panel Mount	No
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	2.40mm
PC Tail Length	3.05mm
Pitch - Mating Interface	0.80mm
Plating min - Mating	0.762µm
Plating min - Termination	0.762µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +85°C
Termination Interface Style	Through Hole - Compliant Pin
Waterproof / Dustproof	No

## Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

---

## Application Tooling

---

This document was generated on Aug 06, 2025