



Image may differ from product. See technical specification for details.

IR 80X90X54

Inner ring for needle roller bearings, IR series

Inner rings for needle roller bearings are available as separate components. They are typically combined with needle roller and cage assemblies or drawn cup needle roller bearings in applications where the shaft cannot be hardened and ground. The inner rings in the IR series are the standard SKF inner rings for needle roller bearings. They are hardened

and ground and have a precision ground raceway surface with a lead-in chamfer on both sides.

- Enable full interchangeability of inner rings
- Standard SKF inner rings for needle roller bearings
- Accommodate axial displacement in both directions
- Chamfers facilitate assembly and protect seal lips during mounting

Overview

Dimensions

Bore diameter	80 mm
Outside diameter	90 mm
Width	54 mm
Raceway diameter	90 mm


Properties

Special raceway feature	None
Radial internal clearance	CN
Tolerance class	Normal
Material	Bearing steel
Coating	Without
Relubrication feature	Without

Logistics

Product net weight	0.55 kg
eClass code	23-05-09-03
UNSPSC code	31171512

Technical specification



Dimensions

d	80 mm	Bore diameter
F	90 mm	Raceway diameter
B	54 mm	Width
r, r _{1,2}	min. 1 mm	Chamfer dimension inner ring

Tolerances and clearances

GENERAL BEARING SPECIFICATIONS

- Tolerances: IR series, LR series, raceways

More Information

 Product details General bearing specifications Designation system	 Engineering information Principles of rolling bearing selection General bearing knowledge Bearing selection process Bearing failure and how to prevent it
---	--



Terms of use

By accessing and using this website / app owned and published by AB SKF (publ.) (556007-3495 · Gothenburg) ("SKF"), you agree to the following terms and conditions:

Warranty Disclaimer and Limitation of Liability

Although every care has been taken to assure the accuracy of the information on this website / app, SKF provides this information "AS IS" and DISCLAIMS ALL WARRANTIES, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE. You acknowledge that your use of this website / app is at your sole risk, that you assume full responsibility for all costs associated with use of this website / app, and that SKF shall not be liable for any direct, incidental, consequential, or indirect damages of any kind arising out of your access to, or use of the information or software made available on this website / app.

Any warranties and representations in this website / app for SKF products or services that you purchase or use will be subject to the agreed upon terms and conditions in the contract for such product or service.

Further, for non-SKF websites / apps that are referenced in our website / app or where a hyperlink appears, SKF makes no warranties concerning the accuracy or reliability of the information in these websites / apps and assumes no responsibility for material created or published by third parties contained therein. In addition, SKF does not warrant that this website / app or these other linked websites / apps are free from viruses or other harmful elements.

Third Party Services

When viewing YouTube content via the SKF website(s) (i.e. using [YouTube API Services](#)), you agree to be bound by the [YouTube Terms of Service](#).

Copyright

Copyright in this website / app copyright of the information and software made available on this website / app rest with SKF or its licensors. All rights are reserved. All licensed material will reference the licensor that has granted SKF the right to use the material. The information and software made available on this website / app may not be reproduced, duplicated, copied, transferred, distributed, stored, modified, downloaded or otherwise exploited for any commercial use without the prior written approval of SKF. However, it may be reproduced, stored and downloaded for use by individuals without prior written approval of SKF. Under no circumstances may this information or software be supplied to third parties.

This website /app includes certain images used under license from Shutterstock, Inc.

Trademarks and Patents

All trademarks, brand names, and corporate logos displayed on the website / app are the property of SKF or its licensors, and may not be used in any way without prior written approval by SKF. All licensed trademarks published on this website / app reference the licensor that has granted SKF the right to use the trademark. Access to this website / app does not grant to the user any license under any patents owned by or licensed to SKF.

Changes

SKF reserves the right to make changes or additions to this website / app at any time.