



Overview

Lead time	Usually in Stock
-----------	------------------

General

Provided equipment	User manual USB cable
--------------------	--------------------------

Physical

Colour	Black
Depth	36.8 cm
Height	26 cm
Net weight	12.1 kg
Width	10 cm

Input

Network frequency	50/60 Hz +/- 3 Hz auto-sensing
Plug standard	IEC 60320 C14
Input voltage limits	176...294 V
Maximum input current	10 A
Switching current capacity	10 A
Input voltage	230 V

Output

Rated power in W	960 W
Maximum configurable power in W	960 W
Output frequency	50/60 Hz +/- 1 Hz sync to mains
UPS type	Line interactive
Nb of power socket outlets	6 IEC 60320 C13 2 IEC 60320 C13 surge
Output voltage	230 V

Conformance

Product certifications	A-Tick C-Tick CE EAC RCM TISI
Marking	GS Mark
Equipment protection policy	Lifetime : 200000 AUD Lifetime : 150000 euros Lifetime : 75000 GBP

Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 % non-condensing
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Acoustic level	45 dBA
Heat dissipation	19.5 Btu/h

Batteries & Runtime

Battery type	Lead-acid battery
Number of battery filled slots	0
Number of battery free slots	0
Battery recharge time	16 h
Number of battery replacement quantity	1
Liquid value	0

Communications & Management

Control panel	Multifunction LCD status and control console
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

Surge Protection and Filtering

Surge energy rate	509 J
Noise suppression	Full time multi-pole noise filtering : 10% of IEEE surge let-through : zero clamping response time: instantaneous
Data line protection	RJ45 10/100/1000 Base-T Ethernet protection

Packing Units

Package 1 Weight	13.75 kg
Package 1 Height	35.9 cm
Package 1 width	22.3 cm
Package 1 Length	48.2 cm
SCC14	10731304346927
Number of Units in Package 2	1
Package 2 Weight	14.61 kg
Package 2 Height	228.60 mm
Package 2 width	482.60 mm
Package 2 Length	381.00 mm

Contractual warranty

Warranty	2 years repair or replace, 3 years repair or replace for European Union countries
----------	---
