



Connectors > PCB Connectors > PCB Headers & Receptacles



PCB Connector Type: **PCB Mount Header**

PCB Mount Orientation: **Vertical**

Connector System: **Wire-to-Board**

Number of Positions: **4**

Centerline (Pitch): **3.96 mm [.156 in]**

Features

Product Type Features

Connector Shape	Rectangular
PCB Connector Type	PCB Mount Header
Connector System	Wire-to-Board
Header Type	Partially Shrouded
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board
Connector Product Type	Housing

Configuration Features

Number of Loaded Positions	2
PCB Mount Orientation	Vertical
Number of Positions	4
Number of Rows	1
Number of Power Positions	4

Electrical Characteristics

--	--



Operating Voltage	250 VDC
-------------------	---------

Body Features

Primary Product Color	Natural
-----------------------	---------

Contact Features

Contact Underplating Material	Nickel
Contact Underplating Material Thickness	.8 – 1.8 µm[31.5 – 70.86 µin]
Contact Size	1.14mm
PCB Contact Termination Area Plating Material Thickness	1 µm[39.37 µin]
Contact Shape & Form	Square
Contact Layout	Inline
Contact Mating Area Length	7.7 mm[.303 in]
Contact Base Material	Brass
Contact Mating Area Plating Material	Tin (Sn)
Contact Mating Area Plating Material Thickness	1 µm[39.37 µin]
Contact Type	Tab
Contact Current Rating (Max)	8 A
PCB Contact Termination Area Plating Material	Tin

Termination Features

Termination Post & Tail Length	3.7 mm[.146 in]
Square Termination Post & Tail Dimension	1.14 mm[.045 in]
Termination Method to PCB	Through Hole - Solder

Mechanical Attachment

Panel Mount Feature	Without
Mating Retention Type	Locking Tab
Mating Alignment Type	Polarization
PCB Mount Alignment	Without
Mating Retention	With
PCB Mount Retention	Without
Connector Mounting Type	Board Mount
Mating Alignment	With

Housing Features

Centerline (Pitch)	3.96 mm[.156 in]
--------------------	------------------



Housing Material	Nylon
------------------	-------

Dimensions

Connector Width	8.5 mm[.334 in]
PCB Thickness (Recommended)	1.6 mm[.063 in]
Connector Height	9.2 mm[.36 in]
Connector Length	15.84 mm[.624 in]

Usage Conditions

Operating Temperature (Max)	105 °C[221 °F]
Operating Temperature Range	-30 – 105 °C[-22 – 221 °F]

Operation/Application

Circuit Application	Power
---------------------	-------

Industry Standards

Glow Wire Rating	Standard Part - Not Glow Wire
UL Flammability Rating	UL 94V-0

Packaging Features

Packaging Quantity	1000
Packaging Method	Bag

Other

Position Locations Omitted	2, 3
Number of Blocked Positions	2

Product Compliance

For compliance documentation, visit the product page on TE.com>




EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Out of Scope
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 265°C



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts

 TE Part # 2316952-4 3.96 EP HDR ASSY 4P, NO PIN 2,3	 TE Part # 1-1123723-4 3.96 EP HDR ASSY 4P(NATURAL)	 TE Part # 5-1123723-4 3.96 EP HDR ASSY 4P(BLACK)	 TE Part # 6-1123723-4 3.96 EP HDR ASSY 4P(GREEN)
 TE Part # 1-1717011-1 EP CONN.HDR ASSY 4/5POS (NATURAL GWT)	 TE Part # 1744494-4 04P EP-II HOUSING, YELLOW	 TE Part # 1-1473057-2 EP CONN HDR 2/4P	 TE Part # 1-1318300-4 3.96 EP HDR ASSY 4P NAT/TUBE
 TE Part # 2-1473059-3 EP CONN.HDR ASSY 3/4P NATURAL (NO.3 POST)	 TE Part # 1-1473059-3 EP CONN POST HDR 3/4P	 TE Part # 1744416-4 4 POS EP II HSG, GLOW WIRE	 TE Part # 1-1565033-2 EP CONN HDR ASSY 2/4P SPECIAL

Also in the Series | Economy Power




Connector Contacts(15)



Connector Hardware(2)



Insertion & Extraction Tools(1)




PCB Headers & Receptacles(483)



Power Contacts(9)




Rectangular Power Connectors(581)




Wire-to-Board Headers & Receptacles (483)

Customers Also Bought



TE Part #84952-4
1MM FPC HORZ.BTTM CONT.ASS.4P



TE Part #284094-8
TERMI-BLOK PCB MOUNT 90, 5,08M



TE Part #1461403-3
OJE-SH-105LMH,000



TE Part #4-2176230-2
3522 2K2 5% 3W



TE Part #3-2176371-3
RQ 0603 10K 0.1% 10PPM 5K RL



TE Part #2-2176372-3
RQ 0603 84K5 0.1% 10PPM 5K RL



TE Part #1462000-1
C93401=MT RELAY 150 MW 5 V

Documents

Product Drawings

04P EP HDR HSG V0 GWT NO 0203P

English

04P EP HDR HSG V0 GWT NO 0203P

English

CAD Files

3D PDF



3D

Customer View Model

[ENG_CVM_CVM_7-1565033-2_AF.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-1565033-2_AF.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_7-1565033-2_AF.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

[Product Specifications](#)

[Application Specification](#)

English