



### Overview

Lead time	Usually in Stock
-----------	------------------

### General

Provided equipment	User manual
--------------------	-------------

### Physical

Cable length	1.83 m
Colour	Black
Depth	21.3 cm
Height	18.5 cm
Net weight	5.2 kg
Width	11.5 cm

### Input

Network frequency	45...65 Hz
Plug standard	IEC 60320 C14
Input voltage limits	160...280 V
Maximum input current	2 A
Switching current capacity	7 A
Input voltage	230 V

### Output

Rated power in W	300 W
Maximum configurable power in W	300 W
Output frequency	50 Hz sync to mains 50 Hz +/- 0.1 % for 50 Hz nominal unsynchronised
UPS type	Line interactive
Wave type	Stepped approximation to a sinewave

Nb of power socket outlets	3 IEC 60320 C13 1 IEC Jumpers
Output voltage	230 V

## Conformance

Product certifications	CE
------------------------	----

## Environmental

Ambient air temperature for operation	0...40 °C
Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...15240.00 m
Acoustic level	45 dBA

## Batteries & Runtime

Number of battery filled slots	0
Number of battery free slots	0
Liquid value	0

## Communications & Management

Control panel	LED status display with on line : on battery : replace battery and overload indicators
Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm

## Surge Protection and Filtering

Surge energy rate	273 J
-------------------	-------

## Packing Units

Package 1 Weight	5.68 kg
Package 1 Height	25.7 cm
Package 1 width	19 cm
Package 1 Length	29.1 cm
SCC14	60731304307367
Number of Units in Package 2	2
Number of Units in Package 3	60

## Offer Sustainability

Sustainable offer status	Green Premium product
REACH free of SVHC	Yes
EU RoHS Directive	Compliant <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	<a href="#">Yes</a>
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Optimized Energy Efficiency	Energy efficient product

## Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------