

Han 24HPR-PFT-for SCL-2xM40-FE-inverse



Image is for illustration purposes only. Please refer to product description.

Part number	19 40 024 1171
Specification	Han 24HPR-PFT-for SCL-2xM40-FE-inverse
HARTING eCatalogue	https://harting.com/19400241171

Identification

Category	Hoods / Housings
Series of hoods/housings	Han [®] HPR
Type of hood/housing	Panel feed through housing
Description of hood/housing	for mounting from outside External FE

Version

Size	24 B
Version	Top entry
Number of cable entries	2
Cable entry	2x M40
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments
Details	The fixing screws must be sealed separately to reach the given degree of protection.

Technical characteristics

Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65 IP68 IP69 / IPX9K acc. to ISO 20653



Pushing Performance
Since 1945

Technical characteristics

Type rating acc. to UL 50 / UL 50E	4 4X 12
Thickness of the panel	≥2 mm

Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (seal)	NBR
Material (locking)	Stainless steel
RoHS	compliant with exemption
RoHS exemptions	6(a) / 6(a)-I: Lead as an alloying element in steel for machining purposes and in galvanised steel containing up to 0,35 % lead by weight / Lead as an alloying element in steel for machining purposes containing up to 0,35 % lead by weight and in batch hot dip galvanised steel components containing up to 0,2 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

Commercial data

Packaging size	1
Net weight	1,249.82 g
Country of origin	China
European customs tariff number	85389099



Pushing Performance
Since 1945

Commercial data

GTIN	5713140279421
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466