


MAG-MATE

TE Internal #: 1217690-1
Poke-In, .43 – .51 mm Magnet Wire, 25.5 – 24 AWG Magnet Wire, Insulation Displacement (IDC), Tin Plating, MAG-MATE, Magnet Wire Terminals

[View on TE.com >](#)



Terminals & Splices > Magnet Wire Terminals



Magnet Wire Terminal Type: **Poke-In**
Compatible With Cavity Size: **Size 2**
Magnet Wire Size: **.43 – .51 mm**
Termination Method to Wire & Cable: **Insulation Displacement (IDC)**

Features

Product Type Features

Compatible With Discrete Wire Type	Magnet Wire, Solid
------------------------------------	--------------------

Body Features

Compatible With Cavity Size	Size 2
-----------------------------	--------

Contact Features

Magnet Wire Terminal Type	Poke-In
Terminal Plating Material	Tin
Contact Underplating Material	Nickel
Terminal Orientation	Twisted

Termination Features

Termination Method to Wire & Cable	Insulation Displacement (IDC)
------------------------------------	-------------------------------

Dimensions

Terminal Height	7.62 mm[.3 in]
Magnet Wire Size	.43 – .51 mm
Stock Thickness (Magnet Wire Side)	.41 mm[.016 in]



Product Length	7.87 mm[.3 in]
----------------	----------------

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-65 – 150 °C[-85 – 302 °F]

Operation/Application

Compatible With Wire Base Material	Copper
------------------------------------	--------

Packaging Features

Packaging Method	Reel, Reel/Carton
------------------	-------------------

Product Compliance

For compliance documentation, visit the product page on TE.com>









EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts




 TE Part # 1217757-1 TERM,POKE-IN,LP, MAG-MATE	 TE Part # 737434-2 MAG-MATE POKE-IN TERMINAL	 TE Part # 1217357-1 MAG-MATE TERM 21-19 0157 TPNBR	 TE Part # 1217689-1 SPECIAL LEAF CONTACT,300 SERIE
 TE Part # 1217068-1 MAG-MATE TERMINAL 19-17 TPBR	 TE Part # 1217942-1 TERMINAL,POKE-IN,MAG-MATE	 TE Part # 1217824-1 TERM,POKE-IN,MAG-MATE	 TE Part # 1742483-1 SPEC LEAF,300 SERIES,MAG-MATE,
 TE Part # 1718165-1 MINI MAG MATE CONTACT (LEAF SPRING)	 TE Part # 1217356-1 MAG-MATE TERM 19-17 0157 TPNBR	 TE Part # 1217358-1 MAG-MATE TERM 23-21 0157 TPNBR	 TE Part # 63754-1 TERM,MAG-MATE 27-23 016TPBR
 TE Part # 62833-2 MAG-MATE POKE-IN TERM 016TPBR	 TE Part # 1217082-1 TERM MAG-MATE 25-22 016 TPPHBZ	 TE Part # 63975-1 MAG-MATE TRI SLOT 016 TPBR	 TE Part # 1217688-1 SPECIAL LEAF CONTACT,300 SERIE
 TE Part # 1217853-1 TERM,SPL,TRI-SLOT,MAG-MATE	 TE Part # 1217355-1 MAG-MATE TERM 16-15 0157 TPNBR		

Also in the Series | **MAG-MATE**



Insertion & Extraction Tools(6)



Magnet Wire Terminals(329)




PCB Terminals(1)

Customers Also Bought



TE Part #CAT-AM71-CH8172
AMP SUPERSEAL 1.5MM,
CONNECTOR HOUSING



TE Part #281934-2
SINGLE WIRE SEAL



TE Part #CAT-D48-ST273
DEUTSCH Solid Contacts



TE Part #DT04-2P
REC, 2P, GRY, N



TE Part #DT06-2S
PLG, 2P, GRY, N



TE Part #CAT-D487-W416
Wedgelocks: DEUTSCH DT



TE Part #114017-ZZ
SEALING PLUG, SIZE 12/16, WHT

Documents

Product Drawings
SPECIAL LEAF CONTACT,300 SERIE
English

CAD Files
3D PDF
3D
Customer View Model
ENG_CVM_CVM_1217690-1_D.2d_dxf.zip
English
Customer View Model
ENG_CVM_CVM_1217690-1_D.3d_igs.zip
English
Customer View Model
ENG_CVM_CVM_1217690-1_D.3d_stp.zip
English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.



Datasheets & Catalog Pages
Magnet Wire Terminals & Splices

English

Product Specifications
Application Specification

English