

S469 - Hi-Vis Reversible Bodywarmer

Collection: 300D Industry High Visibility

Range: High Visibility

Shell Fabric: 300D Industry: 100% Polyester, 300D Oxford Weave with a Stain Resistant finish, Double PU Coated 190g

Lining Fabric: 65% Polyester, 35% Cotton 260g

Filling Fabric: 100% Polyester 200g

Product information

This cleverly designed reversible bodywarmer traps heat to keep you warm when worn either way. The Hi-Vis side of the garment provides added visibility and safety for the wearer when needed. Can interact with style S468.

Standards

EN ISO 20471 Class 2
RIS 3279 TOM Issue 2 (Orange Only)
ANSI/ISEA 107 TYPE R CLASS 2

300D Industry High Visibility

A comprehensive range of single and combination garments in a highly durable, EN343 certified fabric including some new cleverly designed and innovative styles.

High Visibility

Our extensive range of High-Visibility clothing meets stringent requirements in both design and construction, to ensure compliance with the latest EN ISO 20471 & ANSI standards. Innovative and technical, our High Visibility range is ideal for those who will not compromise on style, comfort, protection and performance.

Features

- Extremely water resistant fabric finish, water beads away from fabric surface
- Quilt lined for thermal insulation
- 4 pockets for ample storage
- Reversible garment for multi use
- Interactive inner garment
- Certified to EN ISO 20471 after 50x washes
- Reflective tape for increased visibility
- CE certified
- Available in sizes from XS to 5XL



S469 - Hi-Vis Reversible Bodywarmer
Commodity Code: 6210400000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/15082-01/E00-00

SATRA Technology Centre Ltd (Notified Body No.: AB: 0321)
 SATRA Technology Park
 NN16 8SD, United Kingdom
 Cert No: AB0321/19707-01/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	DUN14
S469ORRS	Orange	65.0	40.0	40.0	0.7000	0.1040	5036108167654	15036108651662
S469ORRM	Orange	65.0	40.0	40.0	0.7780	0.1040	5036108167647	15036108651655
S469ORRL	Orange	65.0	40.0	40.0	0.8160	0.1040	5036108167630	15036108651648
S469ORRXL	Orange	65.0	40.0	40.0	0.8600	0.1040	5036108167661	15036108651679
S469ORRXXL	Orange	65.0	40.0	40.0	0.9140	0.1040	5036108167678	15036108651686
S469ORRXXXL	Orange	65.0	40.0	40.0	0.9040	0.1040	5036108167685	15036108651693
S469ORR4XL	Orange	65.0	40.0	40.0	0.8000	0.1040	5036108167616	15036108755490
S469ORR5XL	Orange	65.0	40.0	40.0	1.0200	0.1040	5036108167623	15036108755506