



SPECIFIC	CATIONS					
RATED OPERATING DISTANCE	10mm = .394"					
MOUNTING MODE	FLUSH					
REPEAT ACCURACY	≤ 2%					
TEMPERATURE DRIFT	≤ ± 10% 3-15%					
HYSTERESIS						
AMBIENT TEMPERATURE	-25°C to +70°C (-13°F to +158°F)					
OPERATING VOLTAGE (VAC/VDC)	20-250 VAC/10-300 VDC					
OPERATIONAL CURRENT (AC/DC)	≤ 400 mA/≤ 300 mA					
MAINS FREQUENCY	50-60 Hz					
RESIDUAL CURRENT	≤ 1.7 mA					
RATED INSULATION VOLTAGE	≤ 1.5 kV					
SURGE CURRENT	≤ 8.0 mA (≤ 10 ms Max. 5 Hz)					
MAX. VOLTAGE DROP	≤ 6.0 V					
OUTPUT FUNCTION	4-WIRE, NORMALLY OPEN					
SMALLES OPERATING CURRENT	≥ 3 mA					
SWITCHING FREQUENCY	≤ 0.02 kHz					
HOUSING MATERAL	PLASTIC, PA12-GF20					
ACTIVE FACE MATERIAL	PLASTIC, PA12-GF30					
END CAP MATERIAL	PLASTIC, EPTR					
CABLE	ø5.2, LifYY, PVC,					
VIBRATION RESISTANCE	55 Hz (IN ALL 3 PLANES)					
SHOCK RESISTANCE	30 g, 11 ms					
PROTECTION DEGREE	IP67					
SWITCHING STATUS INDICATION	LED; YELLOW					

					RELATED DOCUMENTS 1. 2. 3. 4.	3RD ANGLE PROJECTION	THIS DRAWING IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.	High Technolog	RC-HK InC	MINNEAPO 1-800 (763) (763)	AMPUS DRIVE LIS, MN 5544 -544-7769 553-7300 553-0708 fa	41
					SEE SPECIFICATIONS	ALL DIMENSIONS DISPLAYED ON THIS DRAWING ARE FOR	DRFT GMB DSGN	DATE 10/31/88 SCALE 1=1.3 EASUREMENT	Bi10-SI	30-AZ3X		
					FINISH SEE	REFERENCE ONLY CONTACT TURCK		LLIMETER]	IDENTIFICATION NO.	55400	RE'	\
С	UPDATE OPERATING VOLTAGE, SEE ECO	RWC	08/09/07	18320	SPECIFICATIONS	FOR MORE INFORMATION						ر ا
:EV	DESCRIPTION	BY	DATE	ECO NO.			DO NOT SCAL	E THIS DRAWING	FILE: T4355400		SHEET 1 OF	F 1