

Features

- Designed to lock off multiple breakers, switches, and valves with a flexible, multi-stranded steel cable, ensuring secure circuit and system safety during maintenance.
- Features a simple squeeze action lock that allows for easy adjustment and secure locking.
- Built-in hasp accommodates up to six padlocks, making it suitable for group operations where multiple operators need access.
- 4mm PVC-sheathed cable and robust construction offer resistance to wear, chemicals, and environmental factors.
- Suitable for various electrical and mechanical isolation needs, including breakers, switches, and valves.

RS PRO Adjustable Cable Lockout With 3 Mtrs Cable

RS Stock No.: 0276142



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- *The Adjustable Cable Lockout series is specifically designed for locking off multiple breakers, switches, and valves to ensure circuit and system safety during maintenance as part of a safe isolation procedure.*
- *The flexible multi-stranded steel cable with PVC sheath allows for easy threading and can be adjusted to the desired length before locking off with a simple squeeze action.*
- *Simple squeeze action lock.*
- *PVC sheathed multi strand steel cable 4mm diameter.*
- *Ergonomically designed with a built-in hasp that accommodates up to six padlocks, making it suitable for situations where multiple operators are working on the same system.*

General Specifications

Type	Multipurpose Cable Lockout
Material (Yellow Body)	ABS
Material (Black Body)	Nylon
Material (Cable)	Flexible multi-stranded steel cable with PVC sheath
Number of Locks	6
Colour	Yellow and Black

Mechanical Specifications

Hasp Width	30 - 43mm
Hasp Length	123mm
Hasp Depth	12mm
Cable Size	3m
Weight	130 Grams

Operation Environment Specifications

Withstand temperature	-20°C to 80°C (-4°F to 176°F)
-----------------------	-------------------------------