



Fiber Optics > Fiber Optic Connectors > Standard Fiber Connectors > LC Connectors



Compatible Cable Diameter Range: 2.4 mm

Fiber Optic Mode: Multimode

Data Transmission Mode: Simplex

Features

Product Type Features

Fiber Optic Cable Type	Tight Jacket
Fiber Optic Mode	Multimode
Data Transmission Mode	Simplex

Configuration Features

Endface Geometry	PC
------------------	----

Body Features

Primary Product Color	Beige
Boot Type	Bend Limiting
Boot Color	Beige

Dimensions

Boot Length	30.5 mm[1.2 in]
Compatible Cable Diameter Range	2.4 mm

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold




EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2024 (240) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not applicable for solder process capability


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Also in the Series | FullAXS LC



Docking Connectors(1)



LC Connectors(3)

Also in the Series | Sigma SC



High Frequency & RF Inductors(78)



LC Connectors(3)




Printable Tubing(9)



SC Connectors(5)


Customers Also Bought



TE Part #206801-2
AMPLIMITE RECEPT ASY,25 POS



TE Part #321870
TERMINAL SOLIS R 2/0 5/16



TE Part #212447-1
SCREW RTNR KIT,AMPLIMITE



TE Part #321868
TERMINAL SOLIS RING 1/0 3/8




TE Part #965687-1
FIXING RING




TE Part #1658659-1
KIT,HDP-20,ENCLSUR,PLUG,SIZE 3



TE Part #206503-4
RECEPT ASSY,62 POSN,AMPLIMITE



TE Part #206794-4
PIN CONTACT, SZ 20



TE Part #205089-4
HD 20 PIN CONTACT, NON-MAG

Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_1918153-1_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1918153-1_B.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1918153-1_B.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use.

Product Specifications

Product Specification

English

Instruction Sheets



Instruction Sheet (U.S.)

English