

## Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 19.06.2015

Version number 11

Revision: 19.06.2015

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

- **1.1 Product identifier**
- **Trade name: UHU CORRECTION Fluid**
- **1.2 Relevant identified uses of the substance or mixture and uses advised against**  
No further relevant information available.
- **Application of the substance / the mixture** Adhesives
- **1.3 Details of the supplier of the safety data sheet**
- **Manufacturer/Supplier:**  
UHU GmbH & Co.KG  
Herrmannstraße 7  
D-77815 Bühl (Baden)  
Tel.: 0049-(0)7223-284-0  
email: info@uhu.boltongroup.de
- Fax: 0049-(0)7223-284-245
- **Further information obtainable from: CRD**
- **1.4 Emergency telephone number: Tel.: +49 (0) 72 23/28 40**

### SECTION 2: Hazards identification

- **2.1 Classification of the substance or mixture**
- **Classification according to Regulation (EC) No 1272/2008**



GHS02 flame

Flam. Liq. 2          H225 Highly flammable liquid and vapour.



GHS09 environment

Aquatic Chronic 2   H411 Toxic to aquatic life with long lasting effects.



GHS07

 Skin Irrit. 2          H315 Causes skin irritation.  
 STOT SE 3          H336 May cause drowsiness or dizziness.

- **2.2 Label elements**
- **Labelling according to Regulation (EC) No 1272/2008**  
The product is classified and labelled according to the CLP regulation.
- **Hazard pictograms**



GHS02



GHS07



GHS09

- **Signal word** Danger
- **Hazard-determining components of labelling:**  
Hydrocarbons
- **Hazard statements**  
H225 Highly flammable liquid and vapour.  
H315 Causes skin irritation.  
H336 May cause drowsiness or dizziness.  
H411 Toxic to aquatic life with long lasting effects.

(Contd. on page 2)

## Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 19.06.2015

Version number 11

Revision: 19.06.2015

**Trade name: UHU CORRECTION Fluid**

(Contd. of page 1)

**Precautionary statements**

- P101 *If medical advice is needed, have product container or label at hand.*
- P102 *Keep out of reach of children.*
- P103 *Read label before use.*
- P210 *Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking.*
- P261 *Avoid breathing dust/fume/gas/mist/vapours/spray.*
- P280 *Wear protective gloves/protective clothing/eye protection/face protection.*
- P273 *Avoid release to the environment.*
- P303+P361+P353 *IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water/shower.*
- P501 *Dispose of contents/container in accordance with local/regional/national/international regulations.*

**2.3 Other hazards**
**Results of PBT and vPvB assessment**

- **PBT:** Not applicable.
- **vPvB:** Not applicable.

### SECTION 3: Composition/information on ingredients

**3.2 Mixtures**
**Description:**

Solvent mixture with pigment additives  
Adhesive

**Dangerous components:**

EC number: 926-605-8	Hydrocarbons	25-50%
Reg.nr.: 01-2119486291-36-0002		

- **Additional information:** For the wording of the listed risk phrases refer to section 16.

### SECTION 4: First aid measures

**4.1 Description of first aid measures**

- **General information:** Immediately remove any clothing soiled by the product.

**After inhalation:**

*In case of unconsciousness place patient stably in side position for transportation. Supply fresh air; consult doctor in case of complaints.*

- **After skin contact:** Immediately wash with water and soap and rinse thoroughly.

- **After eye contact:** Rinse opened eye for several minutes under running water.

- **After swallowing:** Do not induce vomiting; call for medical help immediately.

**4.2 Most important symptoms and effects, both acute and delayed**

*No further relevant information available.*

**4.3 Indication of any immediate medical attention and special treatment needed**

*No further relevant information available.*

### SECTION 5: Firefighting measures

**5.1 Extinguishing media**

- **Suitable extinguishing agents:** CO<sub>2</sub>, sand, extinguishing powder. Do not use water.

- **For safety reasons unsuitable extinguishing agents:** Water with full jet

**5.2 Special hazards arising from the substance or mixture**

*No further relevant information available.*

(Contd. on page 3)

## Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 19.06.2015

Version number 11

Revision: 19.06.2015

**Trade name: UHU CORRECTION Fluid**

(Contd. of page 2)

- **5.3 Advice for firefighters**
- **Protective equipment:** No special measures required.

### SECTION 6: Accidental release measures

- **6.1 Personal precautions, protective equipment and emergency procedures**  
Ensure adequate ventilation
- **6.2 Environmental precautions:** Do not allow to enter sewers/ surface or ground water.
- **6.3 Methods and material for containment and cleaning up:**  
Do not flush with water or aqueous cleansing agents  
Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).  
Send for recovery or disposal in suitable receptacles.
- **6.4 Reference to other sections**  
See Section 7 for information on safe handling.  
See Section 8 for information on personal protection equipment.  
See Section 13 for disposal information.

### SECTION 7: Handling and storage

- **7.1 Precautions for safe handling**  
Ensure good ventilation/exhaustion at the workplace.  
Prevent formation of aerosols.
- **Information about fire - and explosion protection:**  
Keep ignition sources away - Do not smoke.  
Protect from heat.  
Protect against electrostatic charges.
- **7.2 Conditions for safe storage, including any incompatibilities**
- **Storage:**
- **Requirements to be met by storerooms and receptacles:** Store in a cool location.
- **Information about storage in one common storage facility:** Not required.
- **Further information about storage conditions:**  
Keep container tightly sealed.  
Store in cool, dry conditions in well sealed receptacles.  
Protect from heat and direct sunlight.
- **Storage class:** 3
- **7.3 Specific end use(s)** No further relevant information available.

### SECTION 8: Exposure controls/personal protection

- **Additional information about design of technical facilities:** No further data; see item 7.
- **8.1 Control parameters**
- **Ingredients with limit values that require monitoring at the workplace:**  
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
- **Additional information:** The lists valid during the making were used as basis.
- **8.2 Exposure controls**
- **Personal protective equipment:**
- **General protective and hygienic measures:**  
The usual precautionary measures are to be adhered to when handling chemicals.  
Do not inhale gases / fumes / aerosols.  
Avoid contact with the eyes and skin.  
Avoid direct contact with the chemical/ the product/ the preparation by organisational measures.

(Contd. on page 4)

## Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 19.06.2015

Version number 11

Revision: 19.06.2015

**Trade name: UHU CORRECTION Fluid**

(Contd. of page 3)

- **Protection of hands:**  
 The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.  
 Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation
- **Material of gloves**  
 The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.
- **Penetration time of glove material**  
 The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.
- **Eye protection:** Not required.

### SECTION 9: Physical and chemical properties

#### · 9.1 Information on basic physical and chemical properties

##### · General Information

##### · Appearance:

<b>Form:</b>	Fluid
<b>Colour:</b>	White
<b>Odour:</b>	Petrol-like
<b>Odour threshold:</b>	Not determined.

· **pH-value:** Not determined.

##### · Change in condition

<b>Melting point/Melting range:</b>	Undetermined.
<b>Boiling point/Boiling range:</b>	2501 °C

· **Flash point:** -1 °C

· **Flammability (solid, gaseous):** Not applicable.

· **Ignition temperature:** 460 °C

· **Decomposition temperature:** Not determined.

· **Self-igniting:** Product is not selfigniting.

· **Danger of explosion:** Product is not explosive. However, formation of explosive air/vapour mixtures are possible.

##### · Explosion limits:

<b>Lower:</b>	1,0 Vol %
<b>Upper:</b>	8,3 Vol %

· **Vapour pressure at 20 °C:** 172 hPa

<b>Density at 20 °C:</b>	2,23214 g/cm <sup>3</sup>
<b>Relative density</b>	Not determined.
<b>Vapour density</b>	Not determined.
<b>Evaporation rate</b>	Not determined.

· **Solubility in / Miscibility with water:**

Not miscible or difficult to mix.

· **Partition coefficient (n-octanol/water):** Not determined.

##### · Viscosity:

**Dynamic at 20 °C:** 413 mPas

(Contd. on page 5)

## Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 19.06.2015

Version number 11

Revision: 19.06.2015

**Trade name: UHU CORRECTION Fluid**

(Contd. of page 4)

<b>Kinematic:</b>	Not determined.
<b>· Solvent content:</b>	
<b>Organic solvents:</b>	0,0 %
<b>VOC (EC)</b>	0,00 %
<b>· Solids content:</b>	50,1 %
<b>· 9.2 Other information</b>	No further relevant information available.

### SECTION 10: Stability and reactivity

- **10.1 Reactivity** No further relevant information available.
- **10.2 Chemical stability**
- **Thermal decomposition / conditions to be avoided:**  
No decomposition if used according to specifications.
- **10.3 Possibility of hazardous reactions** No dangerous reactions known.
- **10.4 Conditions to avoid** No further relevant information available.
- **10.5 Incompatible materials:** No further relevant information available.
- **10.6 Hazardous decomposition products:** No dangerous decomposition products known.

### SECTION 11: Toxicological information

- **11.1 Information on toxicological effects**
- **Acute toxicity**
- **Primary irritant effect:**
- **Skin corrosion/irritation**  
Causes skin irritation.
- **Serious eye damage/irritation** Based on available data, the classification criteria are not met.
- **Respiratory or skin sensitisation** Based on available data, the classification criteria are not met.
- **Germ cell mutagenicity** Based on available data, the classification criteria are not met.
- **Carcinogenicity** Based on available data, the classification criteria are not met.
- **Reproductive toxicity** Based on available data, the classification criteria are not met.
- **STOT-single exposure**  
May cause drowsiness or dizziness.
- **STOT-repeated exposure** Based on available data, the classification criteria are not met.
- **Aspiration hazard** Based on available data, the classification criteria are not met.

### SECTION 12: Ecological information

- **12.1 Toxicity**
- **Aquatic toxicity:** No further relevant information available.
- **12.2 Persistence and degradability** No further relevant information available.
- **12.3 Bioaccumulative potential** No further relevant information available.
- **12.4 Mobility in soil** No further relevant information available.
- **Ecotoxicological effects:**
- **Remark:** Toxic for fish
- **Additional ecological information:**
- **General notes:**  
Water hazard class 1 (German Regulation) (Self-assessment): slightly hazardous for water  
Also poisonous for fish and plankton in water bodies.  
Toxic for aquatic organisms  
Do not allow product to reach ground water, water course or sewage system.
- **12.5 Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.

(Contd. on page 6)

## Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 19.06.2015

Version number 11

Revision: 19.06.2015

**Trade name: UHU CORRECTION Fluid**

(Contd. of page 5)

- **12.6 Other adverse effects** No further relevant information available.

### SECTION 13: Disposal considerations

- **13.1 Waste treatment methods**

- **Recommendation**

Must not be disposed together with household garbage. Do not allow product to reach sewage system.

Disposal must be made according to official regulations.

- **European waste catalogue**

08 01 11*	waste paint and varnish containing organic solvents or other dangerous substances
-----------	---

- **Uncleaned packaging:**

- **Recommendation:** Disposal must be made according to official regulations.

### SECTION 14: Transport information

- **14.1 UN-Number**

- **ADR, IMDG, IATA**

UN1263

- **14.2 UN proper shipping name**

- **ADR**

1263 PAINT, ENVIRONMENTALLY HAZARDOUS, special provision 640D

1263 FARBE, UMWELTGEFÄHRDEND, Sondervorschrift 640H

- **IMDG**

PAINT (Hydrocarbons), MARINE POLLUTANT

- **IATA**

PAINT

- **14.3 Transport hazard class(es)**

- **ADR, IMDG**



- **Class**

3 Flammable liquids.

- **Label**

3

- **IATA**



- **Class**

3 Flammable liquids.

- **Label**

3

- **14.4 Packing group**

- **ADR, IMDG, IATA**

II

- **14.5 Environmental hazards:**

Product contains environmentally hazardous substances: Hydrocarbons

- **Marine pollutant:**

Yes

Symbol (fish and tree)

- **Special marking (ADR):**

Symbol (fish and tree)

- **14.6 Special precautions for user**

Warning: Flammable liquids.

- **Danger code (Kemler):**

33

(Contd. on page 7)

## Safety data sheet

according to 1907/2006/EC, Article 31

Printing date 19.06.2015

Version number 11

Revision: 19.06.2015

**Trade name: UHU CORRECTION Fluid**

(Contd. of page 6)

· <b>EMS Number:</b>	F-E,S-E
· <b>14.7 Transport in bulk according to Annex II of Marpol and the IBC Code</b>	Not applicable.
· <b>Transport/Additional information:</b>	
-----	
· <b>ADR</b>	
· <b>Limited quantities (LQ)</b>	5L
· <b>Excepted quantities (EQ)</b>	Code: E2 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 500 ml
· <b>Transport category</b>	2
· <b>Tunnel restriction code</b>	D/E
-----	
· <b>IMDG</b>	
· <b>Limited quantities (LQ)</b>	5L
· <b>Excepted quantities (EQ)</b>	Code: E2 Maximum net quantity per inner packaging: 30 ml Maximum net quantity per outer packaging: 500 ml
· <b>UN "Model Regulation":</b>	UN1263, PAINT, special provision 640D, ENVIRONMENTALLY HAZARDOUS, 3, II

### SECTION 15: Regulatory information

- **15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **Directive 2012/18/EU**
- **Named dangerous substances - ANNEX I** None of the ingredients is listed.
- **15.2 Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

### SECTION 16: Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Relevant phrases**  
H225 Highly flammable liquid and vapour.  
H304 May be fatal if swallowed and enters airways.  
H315 Causes skin irritation.  
H336 May cause drowsiness or dizziness.  
H411 Toxic to aquatic life with long lasting effects.
- **Department issuing MSDS:** CRD
- **Contact:**  
Frau A. Liar,  
Herr Dr. C. Hanf
- **Abbreviations and acronyms:**  
RID: Règlement international concernant le transport des marchandises dangereuses par chemin de fer (Regulations Concerning the International Transport of Dangerous Goods by Rail)  
ICAO: International Civil Aviation Organisation  
ADR: Accord européen sur le transport des marchandises dangereuses par Route (European Agreement concerning the International Carriage of Dangerous Goods by Road)  
IMDG: International Maritime Code for Dangerous Goods  
IATA: International Air Transport Association  
GHS: Globally Harmonised System of Classification and Labelling of Chemicals  
EINECS: European Inventory of Existing Commercial Chemical Substances  
ELINCS: European List of Notified Chemical Substances  
CAS: Chemical Abstracts Service (division of the American Chemical Society)  
VOC: Volatile Organic Compounds (USA, EU)

(Contd. on page 8)

**Safety data sheet**  
according to 1907/2006/EC, Article 31

Printing date 19.06.2015

Version number 11

Revision: 19.06.2015

**Trade name: UHU CORRECTION Fluid**

(Contd. of page 7)

*PBT: Persistent, Bioaccumulative and Toxic**vPvB: very Persistent and very Bioaccumulative**Flam. Liq. 2: Flammable liquids, Hazard Category 2**Skin Irrit. 2: Skin corrosion/irritation, Hazard Category 2**STOT SE 3: Specific target organ toxicity - Single exposure, Hazard Category 3**Asp. Tox. 1: Aspiration hazard, Hazard Category 1**Aquatic Chronic 2: Hazardous to the aquatic environment - Chronic Hazard, Category 2**· \* **Data compared to the previous version altered.***

—ENG—