



Figure similar

SITOR fuse link, with slotted blade contacts, NH1L, In: 250 A, aR, Un DC: 1250 V, front indicator

| Model                                                                  |                                                  |
|------------------------------------------------------------------------|--------------------------------------------------|
| product brand name                                                     | SETRON                                           |
| product designation                                                    | SITOR fuse link                                  |
| design of the product                                                  | With slotted blade contacts                      |
| design of an identification indicator                                  | front indicator                                  |
| design of the switching contact                                        | with slotted blade contacts for M10 screw fixing |
| design of the fuse link                                                | Parallel SITOR semiconductor fuse, LV HRC design |
| General technical data                                                 |                                                  |
| size of fuse system according to EN 60269-1                            | NH1L                                             |
| operating class of the fuse link                                       | aR                                               |
| type of voltage of the operating voltage                               | DC                                               |
| Supply voltage                                                         |                                                  |
| supply voltage                                                         |                                                  |
| • at DC                                                                | 1 250 V                                          |
| Breaking Capacity                                                      |                                                  |
| switching capacity current                                             |                                                  |
| • at DC according to IEC 60947-2 rated value                           | 100 kA                                           |
| Dissipation                                                            |                                                  |
| power loss [W]                                                         | 51 W                                             |
| power loss [W]                                                         |                                                  |
| • for rated value of the current at AC in hot operating state per pole | 51 W                                             |
| • maximum                                                              | 51 W                                             |
| Product details                                                        |                                                  |
| product description                                                    | with bolt-on links, silver-plated                |
| accessories included                                                   | no                                               |
| Mechanical Design                                                      |                                                  |
| mounting position                                                      | Any, preferably vertical                         |
| net weight                                                             | 899 g                                            |
| Environmental conditions                                               |                                                  |
| ambient temperature during operation                                   |                                                  |
| • minimum                                                              | -20 °C                                           |
| • maximum                                                              | 50 °C                                            |
| environmental category                                                 | -20 to +50 at 95% relative humidity              |
| Approvals Certificates                                                 |                                                  |
| General Product Approval                                               | other                                            |



[Confirmation](#)

[Miscellaneous](#)

## Environment



[Environmental Con-  
firmations](#)

## Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NB1128-4KK11>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NB1128-4KK11>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NB1128-4KK11](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NB1128-4KK11)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

4/4/2025 

