



5250
LUMEN



2-16H
RUNTIME



44M
RANGE



IP65/IK07
IP RATING

NEW RL-5250 - INDUSTRIAL 360° LED LANTERN

- 5250 Lumen 50W 160 x SMD LEDs, 6500k
- Dual Power - rechargeable battery and mains powered
- 360° and 180° Lighting modes
- Ultra tough nylon polymer construction
- Milky LED diffuser for even light dispersion
- Stainless steel carry handle on the top
- Concealed ultra tough hanging hook in the base
- Screw hole in the base for attaching to tripods
- IP65 dust & water proof
- IK07 shock resistant
- High power 11.1v 5200mAh Li-ion battery
- 3 Battery level and charging indicator LEDs
- Mains 15V 1.5A multi-country charger/power lead included
- 3 ½ hours charge time

BATTERY 11.1v 5200mAh Rechargeable Li-ion Battery
WEIGHT 1820g
DIMENSION Ø157.5 x H 285.6 mm



3 BATTERY & CHARGE INDICATORS CONCEALED CARRY HANDLE

