



Connectors > Connector Accessories > Connector Hardware



Connector Hardware Accessory Type: **Backplate**

Primary Product Material: **Steel**

Number of Positions: **7529**

Operating Temperature (Max): **100 °C**

Operating Temperature Range: **-40 – 100 °C**

Features

Product Type Features

Connector Hardware Accessory Type	Backplate
Hardware Accessory Function	Mounting

Configuration Features

Number of Positions	7529
---------------------	------

Body Features

Primary Product Plating Material	Nickel
Insulator Material	Polyester
Primary Product Material	Steel

Usage Conditions

Operating Temperature (Max)	100 °C
Operating Temperature Range	-40 – 100 °C

Packaging Features

Packaging Method	Box & Tray
------------------	------------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)



EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 1-2376820-1
[LGA7529 TFLM ASSEMBLY W/O COVER](#)



TE Part # 1-2376820-2
[LGA7529 TFLM ASSEMBLY W/ COVER](#)



TE Part # 2375157-1
[PACKAGE, SOCKET LGA 7529](#)

Customers Also Bought



TE Part #1-770970-0
08P MINI UMN L R/A HDR ASSY SN



TE Part #1977223-6
FSM2JSMASTR=6MM TACT SWITCH,



TE Part #1-2324271-3
RIGHT SEGMENT LGA4189-4 SOCKETP4 FOR ODM



TE Part #1-2324271-4
LEFT SEGMENT LGA4189-4 SOCKET-P4 FOR ODM



TE Part #2328461-2
280 POS., CONNECTOR ASSEMBLY, SLIVER 2.0



TE Part #2-2330551-1
SOCKET P4/P5 BACKPLATE ASSY, STUD 6.02MM




TE Part #2332139-2
RECEPT ASSY, 140 POS, VERT, SLIVER 2.0



TE Part #1-2340321-2
ASSY STRADDLE MOUNT 168P 076 SLIVER 2.0



TE Part #2358256-1
SBCE, 2X25P



TE Part #2379420-2
SOCKET E1 TFLM KIT W/ COVER

Documents

Product Drawings

LGA7529 BACKPLATE ASSY,SHORT STUD

English

CAD Files

Customer View Model

ENG_CVM_CVM_2376821-1_A.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_2376821-1_A.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_2376821-1_A.3d_igs.zip

English

3D PDF

3D

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.