



Housing units PME40-XL-N (Series PME)

four-bolt flanged housing units, cast iron, centring spigot, eccentric locking collar, P seals

The datasheet is only an overview of dimensions and basic load ratings of the selected product. Please always observe all the guidelines in these overview pages. Further information is given on many products under the menu item "Description". You can also order comprehensive information via the Catalogue ordering system (<http://www.ina.de/content.ina.de/en/mediathek/library/library.jsp>) or by telephone on +49 (91 32) 82 - 28 97.

d	40 mm
H	145 mm
B ₁	43,8 mm
A	23 mm
A ₁	11,5 mm
A ₂	1 mm
d ₃ max	58 mm
J	120 mm
N	11,5 mm
Q	M6
S	2 mm
U	31,7 mm
Z	100 mm Tolerance: h8
m	1,62 kg Mass
C _r	34500 N Basic dynamic load rating, radial
C _{0r}	19800 N Basic static load rating, radial
	ME08 Designation of housing
	GRAE40-XL-NPP-B Designation of bearing
	KASK08 Bearing end cap, closed design. To be ordered separately.
	Slot for bearing end cap

