




Connectors > Contacts > Connector Contacts



Contact Type: **Socket**

Contact Retention Within Housing: **Without**

Sealable: **No**

Product Terminates To: **Tube**

Features

Product Type Features

Sealable	No
----------	----

Contact Features

Contact Shape & Form	Round
Barrel Type	Closed
Contact Type	Socket
Contact Retention Within Housing	Without

Termination Features

Product Terminates To	Tube
-----------------------	------

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Packaging Features

Packaging Method	Bag
Packaging Quantity	500

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	



Current ECHA Candidate List: JAN 2025
(247)
Candidate List Declared Against: JUNE
2024 (241)
Does not contain REACH SVHC

Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 1903105-1

PLUG HSG 2P, PNEUMATIC CONN

Customers Also Bought

TE Part #1-1903130-2

DYNAMIC 1200D TAB HSG 4P F/H

TE Part #1318112-1

DYNAMIC D-2 TAB CONT S L/P

TE Part #1-917511-2

DYNAMIC D-3 REC CONT. 2L AU 0.38 L/P

TE Part #CAT-D9934-A15

Contact: Component To Wire; 3-5A, 30-18 Wire Size




TE Part #2-1746741-3
RITS CONN. SOCKET ASSY 3P BLUE




TE Part #1-917807-2
DYNAMIC D-5200M REC HSG 4P X-X



TE Part #1-1747276-4
DYNAMIC D4200 REC HSG 4P/X



TE Part #1747500-2
DYNAMIC D4200 TAB CONT L/LP



TE Part #1-1473562-4
RITS CONN. PLUG ASSY 4P RED

Documents

Product Specifications

Product Specification

Japanese

Instruction Sheets

Instruction Sheet (non U.S.)

Japanese