


TS9256



Temperature cable sensor with process connection

TS-015KIKD06...../US



Product characteristics

Measuring range	-50...250 °C	-58...482 °F
Process connection	clamp adapter Ø 6 mm	
Installation length EL [mm]	50	

Application

Measuring element	1 x Pt 1000; (to DIN EN 60751, class A)
Media	liquids and gases
Minimum installation depth [mm]	15

Electrical data

Protection class	III
------------------	-----

Measuring/setting range

Probe length L	[mm]	50	
Measuring range		-50...250 °C	-58...482 °F
Note on measuring range		stationary: 280 °C / 536 °F (10000 h)	

Accuracy / deviations

Accuracy [K]	$\pm (0,15 K + 0,002 x t)$
--------------	-----------------------------

Response times

Dynamic response T05 / T09 [s]	11 / 37; (to DIN EN 60751)
--------------------------------	----------------------------

Operating conditions

Protection	IP 67
------------	-------

Tests / approvals

MTTF [years]	11415.5
--------------	---------

Mechanical data

Weight [g]	26.4
Housing	cylindrical
Dimensions [mm]	Ø 6 / L = 50
Materials	stainless steel (316Ti/1.4571); PFA/PTFE
Materials (wetted parts)	stainless steel (316Ti/1.4571)
Process connection	clamp adapter Ø 6 mm
Probe diameter [mm]	6
Installation length EL [mm]	50

Remarks

Remarks	The values for accuracy apply to flowing water.
---------	---

TS9256



Temperature cable sensor with process connection

TS-015KIKD06...../US

Pack quantity

1 pcs.

Electrical connection

Cable: 0.15 m, PTFE

Connector: 1 x M12; coding: A



Connection

