



2 YEARS
MANUFACTURER
GUARANTEE

**400
+70
LUMEN**

**80h
MAX.**

270°

270°

USB RECHARGEABLE

0,6m

Product number
EAN

1177370010
4007123691258

TECHNICAL DATA

Luminous flux	400 lm	Battery charging time approx.	3 h
Total luminous flux secondary source	70 lm	Number of batteries	1
Power consumption	3.3 W	Battery type	Built-in battery pack
Colour temperature	6000 K	Battery technology	Lithium-ion
Colour rendering index	80-89 (class 1B)	Fittings	Other
Lifetime	25000 h	Impact strength	IK07
Battery capacity	2 Ah	Protection class	III
Battery voltage	3.7 V	Degree of protection (IP)	IP20
Light duration max.	80 h	Colour	black/grey

PACKAGING, DIMENSIONS AND WEIGHTS

UP	1	Weight of product (including packaging)	0.36 kg
Weight of product (without packaging)	0.22 kg	Dimension LxWxH (incl. packing)	8.7 cm x 6.2 cm x 27.8 cm
Dimension LxWxH (without packing)	3.4 cm x 4.4 cm x 30 cm		