

HALOGEN

FREE

AUTOMOTIVE GRADE Available



## Vishay General Semiconductor

# Low V<sub>F</sub> High Current Density Surface Mount Schottky Barrier Rectifiers

# eSMP<sup>™</sup> Series



DO-220AA (SMP)


PRIMARY CHARACTERISTICS					
I <sub>F(AV)</sub>	1.0 A				
V <sub>RRM</sub>	30 V, 40 V				
I <sub>FSM</sub>	50 A				
E <sub>AS</sub>	11.25 mJ				
V <sub>F</sub>	0.35 V, 0.38 V				
T <sub>J</sub> max.	150 °C				

#### TYPICAL APPLICATIONS

For use in low voltage high frequency inverters, freewheeling, dc-to-dc converters, and polarity protection applications.

#### **FEATURES**

- Very low profile typical height of 1.0 mm
- Ideal for automated placement
- Low forward voltage drop, low power losses



- Low thermal resistance
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified
- Compliant to RoHS directive 2002/95/EC and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21 definition
- Find out more about Vishay's Automotive Grade Product requirements at: www.vishay.com/applications

#### **MECHANICAL DATA**

Case: DO-220AA (SMP)

Molding compound meets UL 94 V-0 flammability rating

Base P/N-M3 - halogen-free and RoHS compliant, commercial grade

Base P/NHM3 - halogen-free and RoHS compliant, automotive grade

**Terminals:** Matte tin plated leads, solderable per J-STD-002 and JESD22-B102

M3 suffix meets JESD 201 class 1A whisker test, HM3 suffix meets JESD 201 class 2 whisker test

Polarity: Color band denotes the cathode end

MAXIMUM RATINGS (T <sub>A</sub> = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	SS1P3L	SS1P4L	UNIT	
Device marking code		13L	14L		
Maximum repetive peak reverse voltage	$V_{RRM}$	30	40	V	
Maximum average forward rectified current (fig. 1) $T_L = 140  ^{\circ}\text{C}$ $T_L = 135  ^{\circ}\text{C}$	I <sub>F(AV)</sub>	1.0 1.5		А	
Peak forward surge current 10 ms single half sine-wave superimposed on rated load	I <sub>FSM</sub>	50		А	
epetitive avalanche energy at I <sub>AS</sub> = 1.5 A, L = 10 mH, T <sub>J</sub> = 25 °C E <sub>AS</sub> 11.25		.25	mJ		
Voltage rate of change (rated V <sub>R</sub> )	dV/dt 10 000		V/µs		
Operating junction and storage temperature range	T <sub>J</sub> , T <sub>STG</sub> - 55 to + 150		°C		

# SS1P3L & SS1P4L

# Vishay General Semiconductor



<b>ELECTRICAL CHARACTERISTICS</b> (T <sub>A</sub> = 25 °C unless otherwise noted)						
PARAMETER	TEST CONDITIONS		SYMBOL	SS1P3L	SS1P4L	UNIT
Maximum instantaneous forward voltage (1)	I <sub>F</sub> = 1.0 A I <sub>F</sub> = 1.0 A	T <sub>J</sub> = 25 °C T <sub>J</sub> = 125 °C	V <sub>F</sub>	0.45 0.35	0.48 0.38	٧
Maximum reverse current at rated V <sub>R</sub> <sup>(2)</sup>		T <sub>J</sub> = 25 °C T <sub>J</sub> = 125 °C	I <sub>R</sub>	200 20	150 15	μA mA
Typical junction capacitance	4.0 V, 1 MHz		CJ	110	130	pF

#### Notes:

 $<sup>^{(2)}</sup>$  Pulse test: Pulse width  $\leq$  40 ms

THERMAL CHARACTERISTICS (T <sub>A</sub> = 25 °C unless otherwise noted)					
PARAMETER	SYMBOL	SS1P3L	SS1P4L	UNIT	
Typical thermal resistance <sup>(1)</sup>	$egin{array}{c} {\sf R}_{ heta {\sf JA}} \ {\sf R}_{ heta {\sf JL}} \ {\sf R}_{ heta {\sf JC}} \end{array}$	105 15 20		°C/W	

#### Note:

<sup>(1)</sup> Thermal resistance from junction to ambient and junction to lead mounted on P.C.B. with 5.0 mm x 5.0 mm copper pad areas.  $R_{\theta JL}$  is measured at the terminal of cathode band.  $R_{\theta JC}$  is measured at the top center of the body

ORDERING INFORMATION (Example)						
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE		
SS1P3L-M3/84A	0.024	84A	3000	7" diameter plastic tape and reel		
SS1P3L-M3/85A	0.024	85A	10 000	13" diameter plastic tape and reel		
SS1P3LHM3/84A (1)	0.024	84A	3000	7" diameter plastic tape and reel		
SS1P3LHM3/85A (1)	0.024	85A	10 000	13" diameter plastic tape and reel		

#### Note:

#### **RATINGS AND CHARACTERISTICS CURVES**

(T<sub>A</sub> = 25 °C unless otherwise noted)




Figure 1. Maximum Forward Current Derating Curve




Figure 2. Maximum Non-Repetitive Peak Forward Surge Current

<sup>(1)</sup> Pulse test: 300 μs pulse width, 1 % duty cycle

<sup>(1)</sup> Automotive grade





# Vishay General Semiconductor




Figure 3. Typical Instantaneous Forward Characteristics




Figure 5. Typical Junction Capacitance




Figure 4. Typical Reverse Leakage Characteristics







Figure 6. Typical Transient Thermal Impedance


#### **PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)

#### DO-220AA (SMP)











Vishay

### **Disclaimer**

All product specifications and data are subject to change without notice.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product.

Vishay disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein to the maximum extent permitted by law. The product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein, which apply to these products.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications unless otherwise expressly indicated. Customers using or selling Vishay products not expressly indicated for use in such applications do so entirely at their own risk and agree to fully indemnify Vishay for any damages arising or resulting from such use or sale. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

Product names and markings noted herein may be trademarks of their respective owners.

Document Number: 91000 Revision: 18-Jul-08

www.vishay.com