

BN-ZB 6,2/WH:UNBEDRUCKT - Marker pin Zack strip



1401831

<https://www.phoenixcontact.com/gb/products/1401831>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker pin Zack strip, Strip, white, unlabeled, can be labeled with: CMS-P1-PLOTTER, mounting type: plug in, for terminal block width: 6.2 mm, Number of individual labels: 10, text field height: 4 mm, text field width: 4 mm

Commercial data

Item number	1401831
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG2112
Product key	BG2112
Catalog page	Page 455 (CL-2007)
GTIN	4017918020576
Weight per piece (including packing)	0.48 g
Weight per piece (excluding packing)	0.44 g
Customs tariff number	39269097
Country of origin	PL

Technical data

Notes

General	Can be labeled with CMS
---------	-------------------------

Product properties

Product type	Terminal marking
Pitch	6.2 mm
Type	high

Marking

Number of individual labels	10
Number of individual labels per row	10
Number of marker strips	10
Identification technology	Plotter

Dimensions

Width	4 mm
Pitch	6.2 mm

Text field

Text field width	4 mm
Text field height	4 mm

Material specifications

Color	white (RAL 9010)
Material	PA
Flammability rating according to UL 94	V2
Components	free from silicone and halogen

Environmental and real-life conditions

UV resistance

Specification	ISO 4892-2:2013-03 (following)
---------------	--------------------------------

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	plug in
---------------	---------

Classifications

ECLASS

ECLASS-13.0	27281101
-------------	----------

ETIM

ETIM 9.0	EC000761
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------