


**Plug-in units type 2 with extraction handle –  
front panel shielded**

**Article number: 20848-498**

- For 6 U, the board location can be moved 1 HP to the right by swapping the upper and lower printed board brackets. This creates space for SMD components on the left-hand side (solder side).

**Delivery quantity: kit**

Item	Qty	Description
1	1	Extraction handle, PPE, grey, at bottom
1a	1	Extraction handle, PPE, grey, at top
2	2	Identification plate, 1.5 mm aluminium, anodised, cut edges clean
3	2	Pivot bush, brass
4	1	Printed board bracket, diecast zinc, at bottom
4a	1	Printed board bracket, diecast zinc, at top
5	-	Printed board bracket, diecast zinc
6	1	U-Front panel for handle, front anodised, rear chromated
7	2	Alignment pin, pressed in, stainless steel
8	2	Sleeve, PA, grey, up to 7 HP front panel width
8	4	Sleeve, PA, grey, up to 8 HP front panel width
9	2	Collar screw, cross recess/slot, nickel-plated steel, M2.5 × 12.3, up to 7 HP front panel width
9	4	Collar screw, cross recess/slot, nickel-plated steel, M2.5 × 12.3, from 8 HP front panel width
11	2	Raised countersunk head screw, M2.5 × 8
12	1	EMC textile seal
13	2	Washer, A2.7
14	2	Pozidrive flathead screw with cross recess, nickel-plated steel, M2.5 × 10

**Technical data:**

Width	Height
12 HP	6 U