

Infotrame DURAFRAME® A4 bulk pack

Article number	488223	Sales unit quantity	1 Pack
Colour	Silver	Sales unit EAN	4005546405858
Packaging unit	10 pieces / 1 pack	Packing weight (gross)	963.1 G
Base EAN	4005546405858	Country of origin	PL



Logos and awards



Product description

- The self-adhesive, A4 format info-frame
- Present information in a high-quality and professional way.
- Quick insertion and replacement of documents via a hinged magnetic frame
- Easy to attach to smooth, stable surfaces without the need for tools and can removed again, e.g. from glass
- Fields of application: For A4 format documents such as room plans, orientation information and offers
- Readability from both sides of glass thanks to 2 inserts
- Identical frame look from both sides
- For portrait and landscape formats
- External dimensions: 236 x 323 mm
- The product is currently undergoing a transition phase: the base material is being changed from PVC to PP. In addition, the previous full-surface lamination is being replaced by a two-strip adhesive application, offering several functional advantages. The transition will be fully completed by the end of 2026 at the latest. Until then, mixed deliveries of the previous and new versions may occur.
- Custom labelling in just a few steps – easily create and print with the free DURAPRINT® design software.

Infotrame DURAFRAME® A4 bulk pack

Product features

Outer width (mm)	236
Outer height (mm)	323
Filling quantity / Filling quantity for	2 Sheet (80 g/sqm)
Format / Format for	A4
Orientation Format	Portrait / landscape
Brand	DURABLE
Width of Visible Area (mm)	205
Height of Visible Area (mm)	290
Frame width (mm)	17
Attachment type	Self-adhesive
Surface product can be used on	Smooth, clean, load-bearing surfaces
Can be removed	On glass
Frame can be opened	Yes
Read from both front and back	Yes
Frame looks identical on both sides	Yes
Anti-glare / minimises reflections	Yes
Write directly on the document inside	No
Reusable	No
Application area	Protected outdoor area
Label type	Download