

8-32448-1 ✓ ACTIVE



PIDG

TE Internal #: 8-32448-1


Blue, Tin, Partially Insulated, 16 – 14 AWG Terminal Knife

Disconnect Splice, 1.04 – 2.62 mm² Wire, 2.05 – 5.18 kcmil, Wire

Insulation Support, PIDG

[View on TE.com >](#)

Terminals & Splices > Knife Disconnects > PIDG Knife Disconnect Splices



Body Plating Material: **Tin**

Wire Insulation Support: **With**

Barrel Color: **Blue**

Compatible Insulation Diameter (Max): **4.32 mm [.17 in]**

Wire Size: **16 – 14 AWG**

[All PIDG Knife Disconnect Splices \(9\)](#)

Features

Body Features

Insulation Material	Nylon
Body Plating Material	Tin

Mechanical Attachment

Wire Insulation Support	With
-------------------------	------

Dimensions

Compatible Insulation Diameter (Max)	4.32 mm [.17 in]
Wire Size	2.05 – 5.18 kcmil

Usage Conditions

Insulation Option	Partially Insulated
-------------------	---------------------

Packaging Features

Packaging Quantity	100
Packaging Method	Loose Piece



Other

Barrel Color	Blue
--------------	------

Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JAN 2025 (247) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability

Product Compliance Disclaimer







This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts





Also in the Series | PIDG



Customers Also Bought





Documents

Product Drawings

[KNIFE DISCONNECT,PIDG 16-14](#)

English

CAD Files

Customer View Model

[ENG_CVM_8-32448-1_G1.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_8-32448-1_G1.3d_stp.zip](#)

English

Customer View Model

[ENG_CVM_8-32448-1_G1.2d_dxf.zip](#)

English

[3D PDF](#)

English

[3D PDF](#)

3D

Customer View Model

[ENG_CVM_CVM_8-32448-1_U.2d_dxf.zip](#)

English

Customer View Model

[ENG_CVM_CVM_8-32448-1_U.3d_igs.zip](#)

English

Customer View Model

[ENG_CVM_CVM_8-32448-1_U.3d_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Instruction Sheets

[Instruction Sheet \(U.S.\)](#)

English

Agency Approvals

[Agency Approval Document](#)

English

8-32448-1

Blue, Tin, Partially Insulated, 16 – 14 AWG Terminal Knife Disconnect Splice, 1.04 – 2.62 mm² Wire, 2.05 – 5.18 kcmil, Wire Insulation Support, PIDG

