





## C(D)Q2K, Compact Cylinder, Double Acting, Single Rod, Non-rotating w/Auto Switch Mounting Groove

### CDQ2KB40TF-20DZ

Datasheet

### General series information

- Double acting, single rod, non-rotating compact cylinder
- Bore sizes (mm): 12, 16, 20, 25, 32, 40, 50, 63
- Standard stroke range (mm): 5 to 100
- Port threads: M (12 to 25 bore); Rc, NPT or G (32 to 63 bore)
- Can mount small auto switches on 4 surfaces.




Double-acting, single-rod cylinder

### Standard specifications

|                                        |                                                 |
|----------------------------------------|-------------------------------------------------|
| Magnet                                 | D (Built-in)                                    |
| Mounting                               | B (Through Hole [Standard; 12 through 63 Bore]) |
| Bore Size                              | Ø40 mm                                          |
| Port Thread Type                       | TF (G)                                          |
| Stroke                                 | 20                                              |
| Body Option                            | Standard (Rod End Female Thread)                |
| Auto Switch Groove                     | Z [Auto Switch Mounting Grooves]                |
| Auto Switch                            | No Switch                                       |
| Lead Wire or Prewired Connector        | 0.5 m or None in the Case of No Switch          |
| Number                                 | 2 pcs.                                          |
| Rod End Options                        | None                                            |
| Pressure medium                        | Compressed air                                  |
| Maximum temperature of pressure medium | 60 °C                                           |
| Minimum temperature of pressure medium | -10 °C [without condensation]                   |
| Maximum operating pressure             | 1.0 MPa                                         |
| Minimum operating pressure             | 0,05 MPa                                        |
| Proof pressure                         | 1.5 MPa                                         |
| Maximum ambient temperature            | 60 °C                                           |


|                                                         |                               |
|---------------------------------------------------------|-------------------------------|
| Minimum ambient temperature                             | -10 °C [without condensation] |
| Number of pneumatic connections                         | 2 pcs.                        |
| Pneumatic input connection                              | G 1/8                         |
| Mode of operation of drive                              | Double acting                 |
| Theoretical cylinder force, advance stroke (at 0.5 MPa) | 628 N                         |
| Theoretical cylinder force, return stroke (at 0.5 MPa)  | 528 N                         |
| Maximum piston speed                                    | 500 mm/s                      |
| Geometric form of the piston rod                        | Single rod                    |
| Male thread of rod end                                  | M14 x 1.5                     |
| Female thread of rod end                                | M8 x 1.25                     |
| Minimum piston speed                                    | 50 mm/s                       |
| Weight                                                  | 0.303 Kg                      |

Dimensions




## Constructions


ø12 to ø25



ø32



ø40 to ø63



### Component Parts

| No. | Description                   | Material                       | Note                           |
|-----|-------------------------------|--------------------------------|--------------------------------|
| 1   | Cylinder tube                 | Aluminum alloy                 | Hard anodised                  |
| 2   | Piston                        | Aluminum alloy                 | Chromated                      |
| 3   | Piston rod                    | Stainless steel                | ø12 to ø25                     |
|     |                               | Carbon steel                   | ø32 to ø63, Hard chrome plated |
|     |                               | Brass                          | ø12, Electroless nickel plated |
| 4   | Rod cover                     | Aluminum alloy                 | ø16 to ø32, Anodised           |
|     |                               | Aluminum alloy                 | ø40 to ø63, Anodised           |
| 5   | Collar                        | Aluminum alloy                 | ø40 to ø63, Anodised           |
| 6   | Retaining ring                | Carbon tool steel              | Phosphate coated               |
| 7   | Bushing                       | Oil-impregnated sintered alloy | ø16 to ø63                     |
| 8   | Hexagon socket head cap screw | Alloy steel                    | ø12 to ø25, Nickel plated      |
| 9   | Hexagon socket head cap screw | Alloy steel                    | ø32, Nickel plated             |
| 10  | Hexagon socket head set screw | Alloy steel                    | ø40 to ø63, Nickel plated      |
| 11  | Magnet                        | —                              |                                |
| 12  | Piston seal                   | NBR                            |                                |
| 13  | Rod seal                      | NBR                            |                                |
| 14  | Tube gasket                   | NBR                            |                                |

## Additional information

Catalogue

[CQ2-Z-C\\_EU.pdf](#)