


# Cam followers



Dimensions				Basic load ratings		Fatigue load limit	Maximum radial loads		Limiting speed	Mass	Designation
D	d	B	C	dynamic C	static C <sub>0</sub>	P <sub>u</sub>	dynamic F <sub>r</sub>	static F <sub>0r</sub>	r/min	kg	-
mm				kN		kN	kN				
26	10	36	12	4,84	6	0,655	9,3	13,2	5300	0,057	KR 26 PPA



**Appertaining grease nipple(s)**

NIP A1x4.5

**Appertaining hexagonal nut**

Size, mm M 10x1  
Rec. tightening torque, Nm 15

**Internal hexagon in stud**

Key width, mm 5