



Part Number : [761505020](#)

Product Description : Impact 100 Ohm 6 Pair Right-Angle Daughtercard Receptacle, Right Guided, 10 Columns, 180 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free

Series Number : 76150

Status : Active

Product Category : Backplane Connectors



Documents & Resources

Drawings

[761505020 sd.pdf](#)

[PK-70873-589-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[SYM-76150-5020-001.zip](#)

[EE-76150-001-002.pdf](#)

[EE-76560-0001-001.pdf](#)

[SP-76150-001-002.zip](#)

[SP-76560-0001-001.zip](#)

Specifications

[AS-76060-990-001.pdf](#)

[AS-76060-9999-001.pdf](#)

[PS-45499-002-001.pdf](#)

[PS-76060-999-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	

	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Backplane Connectors
Series	76150
Description	Impact 100 Ohm 6 Pair Right-Angle Daughtercard Receptacle, Right Guided, 10 Columns, 180 Circuits, Plated Through Hole Dimension 0.39mm, Lead-Free
Application	Conventional, Coplanar, Daughtercard
Component Type	PCB Receptacle
Product Name	Impact
UPC	883906217068

Agency

UL	E29179
----	--------

Electrical

Current - Maximum per Contact	0.75A
Data Rate	25.0 Gbps
Impedance	100Ω
Shielded	No
Shield Type	N/A
Voltage - Maximum	30V AC (RMS)/DC

Physical

Circuits (Loaded)	180
Circuits (maximum)	180
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Flammability	94V-0
Guide to Mating Part	Yes
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	27.622/g
Number of Columns	10
Number of Pairs	6
Number of Rows	18
Orientation	Right Angle
Packaging Type	Tray
PCB Locator	No
PCB Retention	Yes
PCB Thickness - Recommended	1.00mm
PC Tail Length	1.20mm
Pitch - Mating Interface	1.90mm

Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762µm
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-55° to +85°C
Termination Interface Style	Through Hole - Compliant Pin

Mates With / Use With

Mates with Part(s)

Description	Part Number
Impact 100 Ohm 6 Pair Vertical Backplane Headers	<u>76145</u>

Application Tooling

This document was generated on Nov 05, 2025