




Terminals & Splices > Quick Disconnects



Quick Disconnect Terminal Type: **Receptacle**

Wire Size: **1.31 – 3.31 mm²**

Mating Tab Width: **6.35 mm [.25 in]**

Mating Tab Thickness: **.81 mm [.032 in]**

Features

Product Type Features

Insertion Force	Normal
-----------------	--------

Configuration Features

Compatible With Wire & Cable Type	Discrete Wire
Connection Capacity	Single

Contact Features

Quick Disconnect Terminal Type	Receptacle
Mating Tab Width	6.35 mm[.25 in]
Mating Tab Thickness	.81 mm[.032 in]
Terminal Orientation	Straight
Contact Base Material	Brass
Terminal Plating Material	Unplated
Crimp Type	F-Crimp
Barrel Type	Open

Termination Features

--	--



Product Terminates To	Wire & Cable
-----------------------	--------------

Mechanical Attachment

Wire Insulation Support	With
Mating Retention Type	Dimple

Dimensions

Product Length	20.93 mm[.82 in]
Compatible Insulation Diameter Range	5.33 – 6.73 mm[.21 – .265 in]
Terminal Material Thickness	.43 mm[.017 in]
Wire Size	1.31 – 3.31 mm²

Usage Conditions

Insulation Option	Uninsulated
Operating Temperature Range	-40 – 110 °C[-40 – 230 °F]

Industry Standards

Compatible With Agency/Standards Products	CSA, UL
---	---------

Packaging Features

Packaging Quantity	6000
Packaging Method	Strip/Reel

Other

Line	Premier
------	---------

Product Compliance

For compliance documentation, visit the product page on [TE.com](#)>


EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Not applicable for solder process capability



Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



KIT

REPRESENTATION ONLY

TE Part # 7-2150550-7
[OCEAN_2.0_SPARE_PART_KIT-140F300F](#)




TE

TE Part # 2150550-2
[OCEAN_2.0_Applicator-E-140F300F-REA](#)

Also in the Series | FASTON 250



[Compression Connectors\(4\)](#)



[Crimp Terminal Housings\(116\)](#)



[Insertion & Extraction Tools\(6\)](#)



[Insulation Boots & Sleeves\(16\)](#)



[Magnet Wire Terminals\(1\)](#)



[PCB Terminals\(133\)](#)




[Quick Disconnects\(421\)](#)



[Splices\(4\)](#)


Customers Also Bought



TE Part #63895-1
GROUND CLIP 14-18AWG ST



TE Part #1241965-6
STD-TIMER GEH 6P



TE Part #2005248-1
PDL 2P CAP 3.96 F/H(GWT) NAT




TE Part #2296205-2
2P RCPT VAL-U-LOK GWT/V0



TE Part #9-1241961-2
STD TIM HOUSING MKII 2POS




TE Part #2-1241965-4
STD TIMER PLUG HSG 4P W/EXT. LOCKING



TE Part #2029112-3
3P RCPT SR VAL-U-LOK GW



TE Part #2296205-8
8P RCPT VAL-U-LOK GWT/V0



TE Part #794958-3
VAL-U-LOK SKT PHBZ SN 22-26AWG



TE Part #2-1241965-6
6POS STD TIMER HOUSING W.EXT. LOCK

Documents

Product Drawings

250 FASTON REC 16-12 AWG BR

English

CAD Files

Customer View Model

ENG_CVM_CVM_41727_BJ.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_41727_BJ.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_41727_BJ.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

82004 FASTON Terminals (Insulated and Uninsulated) Catalog - FASTON Receptacles Section

English

Product Specifications
Application Specification

English

Agency Approvals
UL Report

English