

DRIVEN BY AIR.



Oil Free Compressors

Offers a robust, reliable, and quieter solution for both trade and DIY workshop applications.



AUDITED



INSPECTED



TESTED



DRIVEN BY AIR.



Simple push on/off button start

User Friendly with clear, easy to read pressure gauges

Lightweight - Can be easily moved around the workshop. Larger 24 litre comes with two wheels

Oil free low maintenance

Compact design, suitable for tight space



6 Litre Oil Free Compressor

RS Code	632-220
Air Receiver	6 Litre
Air Displacement	106 l/min 3.7 cfm
Voltage / Phase	230 v / 50 Hz / Single
Motor	0.8HP 0.55 KW 1,440 RPM
Max Working Pressure	8 bar 116 psi
Sound Pressure Level	72 dBa
Dimensions	50 x 20 x 51 cm
Weight	16 kg

24 Litre Oil Free Compressor

RS Code	632-221
Air Receiver	12 Litre
Air Displacement	138 l/min 4.8 cfm
Voltage / Phase	230 v / 50 Hz / Single
Motor	1HP 0.75 KW 1,440 RPM
Max Working Pressure	8 bar
Sound Pressure Level	72 dBa
Dimensions	59 x 28 x 60 cm
Weight	23 kg