



SD1075 v 1.0 RS 174-5708

RS-GCSP-80 INTERFACE MATERIAL

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830
Date of issue: 15/03/2019 Version: 1.0

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product form : Mixture
Product name : RS-GCSP-80 INTERFACE MATERIAL
Product code : GCSP-80
Type of product : Thermal interface material, Fillers, putties, plasters, modelling clay

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.2.1. Relevant identified uses

Main use category : Professional use
Use of the substance/mixture : Conductive agents
Fillers
Function or use category : Conductive agents, Fillers

1.2.2. Uses advised against

No additional information available

1.3. Details of the supplier of the safety data sheet

UK

RS Components Ltd
Birchington Road
Corby
Northants
NN17 9RS
Tel: +44 (0) 845 850 9900
RCustomerServicesUK@rs-components.com

Ireland

RS Components Ltd
Glenview Industrial Estate
Herberton Road
Rialto
Dublin 12
Tel No +353 (0) 1 415 3100
enquiries.ie@rs-components.com

www.rs-online.com

1.4. Emergency telephone number

Emergency number : +44 1865 407333 (24hr)

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification according to Regulation (EC) No. 1272/2008 [CLP]

Not classified

Adverse physicochemical, human health and environmental effects

To our knowledge, this product does not present any particular risk, provided it is handled in accordance with good occupational hygiene and safety practice.

2.2. Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

No labelling applicable

2.3. Other hazards

No additional information available

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	Classification according to Regulation (EC) No. 1272/2008 [CLP]
ALUMINIUM OXIDE	(CAS-No.) 1302-74-5	80 - 95	Not classified
SILICONE B	(CAS-No.) 67763-03-05	5 - 20	Not classified

RS-GCSP-80 INTERFACE MATERIAL

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 4: First aid measures

4.1. Description of first aid measures

First-aid measures after inhalation	: Remove person to fresh air and keep comfortable for breathing.
First-aid measures after skin contact	: Wash skin with plenty of water.
First-aid measures after eye contact	: Rinse eyes with water as a precaution.
First-aid measures after ingestion	: Call a poison center or a doctor if you feel unwell.

4.2. Most important symptoms and effects, both acute and delayed

Symptoms/effects after inhalation	: Inhalation may cause irritation (cough, short breathing, difficulty in breathing).
Symptoms/effects after skin contact	: Causes mild skin irritation.
Symptoms/effects after eye contact	: mild eye irritation.
Symptoms/effects after ingestion	: May cause irritation to the digestive tract. Abdominal pain, nausea.

4.3. Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media	: Water spray. Dry powder. Foam.
------------------------------	----------------------------------

5.2. Special hazards arising from the substance or mixture

Hazardous decomposition products in case of fire	: Toxic fumes may be released.
--	--------------------------------

5.3. Advice for firefighters

Protection during firefighting	: Do not attempt to take action without suitable protective equipment. Self-contained breathing apparatus. Complete protective clothing.
--------------------------------	--

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

6.1.1. For non-emergency personnel

Emergency procedures	: Ventilate spillage area.
----------------------	----------------------------

6.1.2. For emergency responders

Protective equipment	: Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".
----------------------	---

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up	: Mechanically recover the product.
Other information	: Dispose of materials or solid residues at an authorized site.

6.4. Reference to other sections

For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling	: Ensure good ventilation of the work station. Wear personal protective equipment.
Hygiene measures	: Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions	: Store in a well-ventilated place. Keep cool.
--------------------	--

7.3. Specific end use(s)

No additional information available

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

ALUMINIUM OXIDE (1302-74-5)

Austria	Local name	Aluminiumoxid und Aluminiumhydroxid
Austria	MAK (mg/m ³)	5 mg/m ³
Austria	MAK Short time value (mg/m ³)	10 mg/m ³
Austria	Regulatory reference	BGBl. II Nr. 186/2015
Croatia	Local name	Prašina smirka (korund)

RS-GCSP-80 INTERFACE MATERIAL

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

ALUMINIUM OXIDE (1302-74-5)

Croatia	GVI (granična vrijednost izloženosti) (mg/m ³)	10 mg/m ³ U (ukupna prašina) 4 mg/m ³ R (respirabilna prašina)
Croatia	Regulatory reference	Pravilnik o izmjenama i dopunama Pravilnika o graničnim vrijednostima izloženosti opasnim tvarima pri radu i o biološkim graničnim vrijednostima (NN, br. 75/13)
Germany	TRGS 910 Acceptable concentration notes	
Greece	Local name	Emery
Greece	OEL TWA (mg/m ³)	5 mg/m ³ αναπν. 10 mg/m ³ εισπν.
Greece	Regulatory reference	Π.Δ. 90/1999
Ireland	Local name	Emery
Ireland	OEL (8 hours ref) (mg/m ³)	10 mg/m ³ total inhalable dust 4 mg/m ³ respirable dust
Ireland	Regulatory reference	Code of Practice for the Chemical Agents Regulations 2018
Spain	Local name	Esmeril
Spain	VLA-ED (mg/m ³)	10 mg/m ³ polvo
Spain	Notes	e (Este valor es para la materia particulada que no contenga amianto y menos de un 1% de sílice cristalina).
Spain	Regulatory reference	Límites de Exposición Profesional para Agentes Químicos en España 2018. INSHT
United Kingdom	Local name	Emery
United Kingdom	WEL TWA (mg/m ³)	4 mg/m ³ respirable 10 mg/m ³ inhalable dust
United Kingdom	Regulatory reference	EH40/2005 (Third edition, 2018). HSE
Switzerland	Local name	Aluminium oxyde / Aluminiumoxid [Korund]
Switzerland	MAK (mg/m ³)	3 mg/m ³ (a) / (a)
Switzerland	Critical toxicity	Formel / Formal
Switzerland	Notation	B / B
Switzerland	Remark	NIOSH
Switzerland	Regulatory reference	www.suva.ch, 01.11.2018

8.2. Exposure controls

Appropriate engineering controls:

Ensure good ventilation of the work station.

Personal protective equipment:

Gloves. Safety glasses.

Materials for protective clothing:

Use personal protective clothing as required

Hand protection:

Protective gloves

Type	Material	Permeation	Thickness (mm)	Penetration	Standard
Disposable gloves	Nitrile rubber (NBR)	6 (> 480 minutes)	0.11		EN 374-2

Eye protection:

Safety glasses

Type	Use	Characteristics	Standard
Safety glasses	Dust	clear	EN 166

RS-GCSP-80 INTERFACE MATERIAL

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Skin and body protection:

Wear suitable protective clothing

Respiratory protection:

In case of insufficient ventilation, wear suitable respiratory equipment

Device	Filter type	Condition	Standard
Air-Purifying Respirator (APR), disposable	Type P3	Dust protection	EN 14387

Personal protective equipment symbol(s):



Environmental exposure controls:

Avoid release to the environment.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state	: Solid
Colour	: Grey.
Odour	: odourless.
Odour threshold	: No data available
pH	: Approx. 7
Relative evaporation rate (butylacetate=1)	: No data available
Melting point	: No data available
Freezing point	: Not applicable
Boiling point	: > 35 °C
Flash point	: > 93 °C
Auto-ignition temperature	: Not applicable
Decomposition temperature	: No data available
Flammability (solid, gas)	: Non flammable.
Vapour pressure	: No data available
Relative vapour density at 20 °C	: No data available
Relative density	: 2.75
Solubility	: No data available
Log Pow	: No data available
Viscosity, kinematic	: No data available
Viscosity, dynamic	: No data available
Explosive properties	: No data available
Oxidising properties	: No data available
Explosive limits	: Not applicable

9.2. Other information

No additional information available

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

None under recommended storage and handling conditions (see section 7).

10.5. Incompatible materials

No additional information available

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

RS-GCSP-80 INTERFACE MATERIAL

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	: Not classified
Acute toxicity (dermal)	: Not classified
Acute toxicity (inhalation)	: Not classified
Skin corrosion/irritation	: Not classified
	pH: Approx. 7
Serious eye damage/irritation	: Not classified
	pH: Approx. 7
Respiratory or skin sensitisation	: Not classified
Germ cell mutagenicity	: Not classified
Carcinogenicity	: Not classified
Reproductive toxicity	: Not classified
STOT-single exposure	: Not classified
STOT-repeated exposure	: Not classified
Aspiration hazard	: Not classified

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general	: The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
Acute aquatic toxicity	: Not classified
Chronic aquatic toxicity	: Not classified

12.2. Persistence and degradability

No additional information available

12.3. Bioaccumulative potential

No additional information available

12.4. Mobility in soil

No additional information available

12.5. Results of PBT and vPvB assessment

No additional information available

12.6. Other adverse effects

No additional information available

SECTION 13: Disposal considerations

13.1. Waste treatment methods

Waste treatment methods	: Dispose of contents/container in accordance with licensed collector's sorting instructions.
-------------------------	---

SECTION 14: Transport information

In accordance with ADR / RID / IMDG / IATA / ADN

ADR	IMDG	IATA	ADN	RID
14.1. UN number				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.2. UN proper shipping name				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.3. Transport hazard class(es)				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.4. Packing group				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
14.5. Environmental hazards				
Not regulated	Not regulated	Not regulated	Not regulated	Not regulated
No supplementary information available				
14.6. Special precautions for user				

Overland transport

Not regulated

RS-GCSP-80 INTERFACE MATERIAL

Safety Data Sheet

according to Regulation (EC) No. 1907/2006 (REACH) with its amendment Regulation (EU) 2015/830

Transport by sea

Not regulated

Air transport

Not regulated

Inland waterway transport

Not regulated

Rail transport

Not regulated

14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.1.1. EU-Regulations

Contains no REACH substances with Annex XVII restrictions

Contains no substance on the REACH candidate list

Contains no REACH Annex XIV substances

Contains no substance subject to REGULATION (EU) No 649/2012 OF THE EUROPEAN PARLIAMENT AND OF THE COUNCIL of 4 July 2012 concerning the export and import of hazardous chemicals.

Substance(s) are not subject to Regulation (EC) No 850/2004 of the European Parliament and of the Council of 29 April 2004 on persistent organic pollutants and amending Directive 79/117/EEC.

15.1.2. National regulations

Germany

Reference to AwSV

: Water hazard class (WGK) 3, Highly hazardous to water (Classification according to AwSV, Annex 1)

12th Ordinance Implementing the Federal Immission Control Act - 12.BImSchV

: Is not subject of the 12. BImSchV (Hazardous Incident Ordinance)

Netherlands

SZW-lijst van kankerverwekkende stoffen

: None of the components are listed

SZW-lijst van mutagene stoffen

: None of the components are listed

NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Borstvoeding

: None of the components are listed

NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Vruchtbaarheid

: None of the components are listed

NIET-limitatieve lijst van voor de voortplanting giftige stoffen – Ontwikkeling

: None of the components are listed

Denmark

Classification remarks

: Emergency management guidelines for the storage of flammable liquids must be followed

15.2. Chemical safety assessment

No chemical safety assessment has been carried out

SECTION 16: Other information

No additional information available

SDS EU (REACH Annex II)

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product