

DC/DC Converter

THM 3WI Series, 3 Watt

- Ultra wide 4:1 input voltage 3 W DC/DC converter in a compact DIP-24 plastic case
- I/O isolation 5000 VACrms rated for 250 VACrms working voltage
- Certification according to IEC/EN/ES 60601-1 3rd edition for 2xMOPP
- Risk management process according to ISO 14971 including risk management file
- Acceptance criteria for electronic assemblies according to IPC-A-610 Level 3
- Low leakage current < 2µA
- Extended operating temperature range -40°C to 90°C.
- EMC compliance to IEC 60601-1-2 4th edition and EN55032 class A
- Operating up to 5000m altitude
- 5 year product warranty



The THM-3WI series is a range of medical 3 Watt DC/DC converters in DIP-24 plastic package and with ultra-wide 4:1 input voltage range. They provide a reinforced isolation system for 5000 VACrms isolation and a very low leakage current of less than 2 µA. The units are approved to IEC/EN/ES 60601-1 3rd edition for 2 × MOPP (Means Of Patient Protection) and come along with an ISO 14971 risk management file. Design and production conform to the quality management system ISO 13485. With a high efficiency of up to 87% and highest grade components the converters can reliably operate in an ambient temperature range of -40°C up to +90°C. They constitute a reliable solution not only for medical equipment but also for demanding ranges of application such as transportation, control & measurement or IGBT drivers.

Models

Order code*	Input voltage range	Output voltage	Output current max.	Efficiency typ.
THM 3-0510WI	4.5 – 9 VDC (5 VDC nominal)	3.3 VDC	1000 mA	81.0 %
THM 3-0511WI		5.0 VDC	600 mA	84.5 %
THM 3-0512WI		12 VDC	250 mA	85.5 %
THM 3-0513WI		15 VDC	200 mA	87.5 %
THM 3-0515WI		24 VDC	125 mA	85.5 %
THM 3-0521WI		±5.0 VDC	±300 mA	83.0 %
THM 3-0522WI		±12 VDC	±125 mA	86.0 %
THM 3-0523WI		±15 VDC	±100 mA	86.0 %
THM 3-2410WI	9.0 – 36 VDC (24 VDC nominal)	3.3 VDC	1000 mA	82.0 %
THM 3-2411WI		5.0 VDC	600 mA	84.5 %
THM 3-2412WI		12 VDC	250 mA	87.0 %
THM 3-2413WI		15 VDC	200 mA	87.0 %
THM 3-2415WI		24 VDC	125 mA	87.0 %
THM 3-2421WI		±5.0 VDC	±300 mA	83.0 %
THM 3-2422WI		±12 VDC	±125 mA	87.5 %
THM 3-2423WI		±15 VDC	±100 mA	86.0 %
THM 3-4810WI	18 – 75 VDC (48 VDC nominal)	3.3 VDC	1000 mA	81.0 %
THM 3-4811WI		5.0 VDC	600 mA	84.0 %
THM 3-4812WI		12 VDC	250 mA	87.0 %
THM 3-4813WI		15 VDC	200 mA	86.5 %
THM 3-4815WI		24 VDC	125 mA	86.5 %
THM 3-4821WI		±5.0 VDC	±300 mA	83.0 %
THM 3-4822WI		±12 VDC	±125 mA	86.0 %
THM 3-4823WI		±15 VDC	±100 mA	86.0 %

* Suffix **-B2** for trim option with adjustable output
 Suffix **-B3** for remote control option
 Suffix **-B4** for trim + remote-control option

Input Specifications

Input current no load	5 Vin models:	20 mA typ.
	24 Vin models:	6 mA typ.
	48 Vin models:	4 mA typ.
Surge voltage (3 s max.)	5 Vin models:	16 V max.
	24 Vin models:	50 V max.
	48 Vin models:	100 V max.
Start-up voltage	5 Vin models:	4.5 VDC (or lower)
	24 Vin models:	9 VDC (or lower)
	48 Vin models:	18 VDC (or lower)
Startup time		30 ms
Under voltage shut down	5 Vin models:	4 VDC typ.
	24 Vin models:	8 VDC typ.
	48 Vin models:	16 VDC typ.
EMC emissions	– Conducted & Radiated input suppression	EN 55011 limits to IEC 60601-1-2 4th edition
	– Application note for filter class B proposal	EN 55032 class A (internal filter) www.tracopower.com/overview/thm3wi
EMC immunity	– Generic for Medical equipment	IEC/EN 60601-1-2 4th edition
	– ESD (electrostatic discharge)	EN 61000-4-2, air ± 8 kV, contact ± 6 kV, perf. criteria A
	– Radiated immunity	EN 61000-4-3, 10 V/m, perf. criteria A
	– Fast transient / surge (with external input capacitor / diode)	EN 61000-4-4, ± 2 kV, perf. criteria A
		EN 61000-4-5, ± 2 kV perf. criteria A
	5 Vin models:	Nippon chemi-con KY 1000 μ F/ 25 V and reverse diode (Vishay V10P45) in parallel
	24 Vin models:	Nippon chemi-con KY 470 μ F/ 50 V
	48 Vin models:	Nippon chemi-con KY 330 μ F/ 100 V
	– Conducted immunity	EN 61000-4-6, 10 Vrms, perf. criteria A
	– Magnetic field immunity	EN 61000-4-8
External input fuse required (recommended values, slow blow type)	5 Vin models:	1.6 A
	24 Vin models:	0.8 A
	48 Vin models:	0.5 A

Output Specifications

Voltage set accuracy		±1 % max.
Output voltage adjustment (for THM 3WI -B2 / -B4 option models only)		
– Single output	15 & 24 Vout models:	–10 / +20%
	other models:	±10%
– Dual output	5, 12 & 15 Vout models:	±10%
Regulation	– Input variation	single output: 0.2 % max. dual output: 0.5 % max.
	– Load variation (0 – 100 %)	single output: 0.2 % max. dual output: 1.0 % max.
	– Cross regulation	dual output: 5.0 % max. (asymmetrical load 25/100 %)
Minimum load		not required
Ripple and noise (20 MHz Bandwidth)	3.3 & 5.0 Vout models:	30 mVp-p typ. with cap. 10 µF/25 V X7R MLCC
	12 & 15 Vout models:	40 mVp-p typ. with cap. 10 µF/25 V X7R MLCC
	24 Vout models:	50 mVp-p typ. with cap. 4.7 µF/50 V X7R MLCC
Transient response	– Recovery time (25% load step change)	250 µs typ.
Over load protection		at 150 % typ. of I _{out} rated (hiccup mode)
Short circuit protection		Continuous, automatic recovery
Over voltage protection	– Single output	3.3 Vout models: 3.7 – 5.0 VDC
		5.0 Vout models: 5.6 – 7.0 VDC
		12 Vout models: 13.5 – 16.0 VDC
		15 Vout models: 18.3 – 22.0 VDC
		24 Vout models: 29.1 – 34.5 VDC
	– Dual output	±5 Vout models: 5.6 – 7.0 VDC
		±12 Vout models: 13.5 – 18.2 VDC
		±15 Vout models: 17.0 – 22.0 VDC

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

General Specifications

Capacitive load	– Single output	3.3 Vout models: 1'050 µF max. 5.0 Vout models: 750 µF max. 12 Vout models: 130 µF max. 15 Vout models: 100 µF max. 24 Vout models: 39 µF max.
	– Dual output	±5 Vout models: 430 µF max. (each output) ±12 Vout models: 75 µF max. (each output) ±15 Vout models: 56 µF max. (each output)
Temperature ranges	– Industrial / Commercial rating	–40°C to +90°C (without derating)
	– Medical IEC/EN 60601-1 rating	–40°C to +80°C (without derating)
	– Case temperature	+105°C max.
	– Storage temperature	–55°C to +125°C
Thermal impedance		18°C/W
Humidity (non condensing)		5 % to 95 % rel H max.
Isolation voltage (50 Hz, 60 s)	– to meet ES/IEC/EN 60601-1	5000 VACrms, rated for 250 VACrms working voltage, 2 × MOPP
Clearance/creepage		8 mm min.
Leakagecurrent (at 240 VAC, 60 Hz)		2 µA max.
Isolation capacitance (input/output)		17 pF max.
Altitude during operation		5000 m
Temperature coefficient		±0.02 %/K typ.
Reliability, calculated MTBF (MIL-HDBK-217F at +25°C, ground benign)		6'400'000 h
Switching frequency		150 kHz ±15 kHz (pulse width modulation)
Vibration and thermal shock resistance		according to MIL-STD-810F
Remote On/Off (for THM 3WI -B3 / -B4 option models only)	– Off	2.2 – 12 VDC (referred to -Vin pin)
	– On	open circuit or 0 – 1.2 VDC (referred to -Vin pin)
	– Off idle current	2.5 mA typ.
	– Remote pin input current	–0.5 mA min. 1 mA max.
Safety standards/approvals	– Medical equipment	ANSI/AAMI ES60601-1:2005/(R)2012, IEC/EN60601-1 3rd edition
	– Certification documents	www.tracopower.com/overview/thm3wi
Environmental compliance	– Reach	www.tracopower.com/info/reach-declaration.pdf
	– RoHS	RoHS directive 2011/65/EU

Physical Specifications

Casing material	non-conductive black plastic
Base material	non-conductive black plastic
Potting material	silicone (UL94 V-0 rated)
Package weight	14 g (0.48 oz)
Soldering temperature	265°C / 10 s max.




- The component is not be used in an oxygen rich environment.
- The component is not to be used in conjunction with flammable anaesthetics and agents.
- The component has to be disposed appropriately. Please refer to local regulations (Waste Electrical and Electronic Equipment).
- A modification of the component is not allowed.

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

Outline Dimensions


Standard pinning with options: suffix **-B2** (with Trim); **-B3** (with Remote); **-B4** (with Trim and Remote)



Standard Pinout		
Pin	Single	Dual
1	No Pin*/Remote	No Pin*/Remote
2	-Vin (GND)	-Vin (GND)
10	No Pin*/Trim	No Pin*/Trim
11	No con.	-Vout
14	+Vout	+Vout
16	-Vout	Common
22	+Vin (Vcc)	+Vin (Vcc)
23	+Vin (Vcc)	+Vin (Vcc)

*If Remote or Trim is not selected there is no pin on corresponding number

Optional pinning: suffix **-A1**



Optional Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
11	No pin	Common
12	-Vout	No pin
13	+Vout	-Vout
15	No pin	+Vout
23	-Vin (GND)	-Vin (GND)
24	-Vin (GND)	-Vin (GND)

Remark: No suffix **-A1** for 5 Vin models. Corresponding parts are with THM 3 series by default. see www.tracopower.com/overview/thm3

Dimensions in [mm], () = Inch
Tolerances ± 0.5 (± 0.02)
Pin $\varnothing 0.6 \pm 0.1$ (0.024 ± 0.004)
Pin pitch tolerances ± 0.25 (± 0.01)