



Connectors > RF Connectors > Coax Connectors > MMCX Plug Connector



RF Interface: **MMCX**

RF Connector Style: **Plug**

RF Connector Mated Outer Diameter (Approximate): **2.7 mm [ .106 in ]**

Impedance: **50 Ω**

RF Connector Coupling Mechanism: **Push-On**

[All MMCX Plug Connector \(3\)](#)

Features

Product Type Features

RF Interface	MMCX
RF Connector Style	Plug
Connector System	Cable-to-Board
Sealable	No
Connector & Contact Terminates To	Printed Circuit Board

Configuration Features

PCB Mount Orientation	Vertical
Number of Positions	1
Number of Coaxial Contacts	1

Electrical Characteristics

Impedance	50 Ω
-----------	------

Body Features

Body Material	Brass
---------------	-------



Body Plating Material	Gold
-----------------------	------

Contact Features

RF Connector Center Contact Underplating Material	Nickel
RF Connector Center Contact Plating Material	Gold (Au)
RF Connector Center Contact Material	Brass

Termination Features

Termination Method to PCB	Surface Mount
Termination Post & Tail Length	3 mm[.118 in]

Mechanical Attachment

RF Connector Coupling Mechanism	Push-On
Connector Mounting Type	Panel Mount
RF Contact Captivation Method	Mechanical
Detent	Without

Dimensions

Profile Height from PCB	4.5 mm[.177 in]
RF Connector Mated Outer Diameter (Approximate)	2.7 mm[.106 in]

Operation/Application

Operating Frequency	6 GHz
---------------------	-------

Packaging Features

Packaging Method	Bag
------------------	-----

Other

Dielectric Material	PTFE
---------------------	------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant with Exemptions
EU ELV Directive 2000/53/EC	Compliant with Exemptions
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUL 2021 (219) SVHC > Threshold: Pb (3.7% in Component Part)



Article Safe Usage Statements:  
Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location.

Halogen Content	Low Bromine/Chlorine - Br and Cl < 900 ppm per homogenous material. Also BFR /CFR/PVC Free
Solder Process Capability	Pin-in-Paste capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Customers Also Bought

TE Part #1408149-1  
MMCX RT ANGLE PLUG - CRIMP ATT

TE Part #2-966067-5  
FER,WIRE,PL SLV,10.00/8,L18,RED,LP

TE Part #8-34158-1  
TERMINAL,PG R 16-14 6

TE Part #338728-8  
MICROM. MOB SMD CON

TE Part #9-1625868-3  
RP 2A 0.25W 48R7 0.1% 25PPM 1K RL

TE Part #5-2176325-2  
CRGP 0402 180K 1%

TE Part #2-1879352-7  
RR02 5% 3R9 AMMO

TE Part #3-2172093-2  
M8.MALE.PNLREAR.4POS.RA. PCBSTND.SHLD

TE Part #4-1879233-6  
SMW5 7R5 5%

TE Part #8-1879132-9  
RN 0402 18K7 0.1% 10PPM 5K RL



Documents

Product Drawings

MMCX STRAIGHT PCB PLUG

English

CAD Files

3D PDF

3D

Customer View Model

ENG\_CVM\_CVM\_1408496-1\_B.2d\_dxf.zip

English

Customer View Model

ENG\_CVM\_CVM\_1408496-1\_B.3d\_igs.zip

English

Customer View Model

ENG\_CVM\_CVM\_1408496-1\_B.3d\_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

MCX Connectors

English

Product Specifications

Product Specification

English