


## IIS205

IIB3022-BPKG/US-104

Inductive sensors



### Product characteristics

Inductive sensor

Metal thread M30 x 1.5

Connector

Increased sensing range

Gold-plated contacts

Sensing range 22 mm; [nf] non-flush mountable

### Electrical data

Electrical design	DC PNP
Operating voltage [V]	10...30 DC
Current consumption [mA]	< 10
Protection class	II
Reverse polarity protection	yes

### Outputs

Output function	normally open
Voltage drop [V]	< 2.5
Current rating [mA]	100
Short-circuit protection	yes
Overload protection	yes
Switching frequency [Hz]	100

### Range

Sensing range [mm]	22
Real sensing range (Sr) [mm]	22 ± 10 %
Operating distance [mm]	0...17.82

### Accuracy / deviations

Correction factors	mild steel = 1 / stainless steel approx. 0.7 / brass approx. 0.5 / Al approx. 0.4 / Cu approx. 0.3
Hysteresis [% of Sr]	3...15
Switch-point drift [% of Sr]	-10...10

### Environment

Ambient temperature [°C]	-25...70
Protection	IP 67

### Tests / approvals

EMC	EN 61000-4-2 ESD: 4 kV CD / 8 kV AD EN 61000-4-3 HF radiated: 10 V/m EN 61000-4-4 Burst: 2 kV EN 61000-4-6 HF conducted: 10 V EN 55011: class B
-----	---

# IIS205

IIB3022-BPKG/US-104

**Inductive sensors**

MTTF	[Years]	1570
UL approval number		A001

## Mechanical data

Mounting	non-flush mountable  Brass white bronze coated; active face: PBT orange; LED window: PEI; lock nuts: Brass white bronze coated
Housing materials	
Weight [kg]	


## Displays / operating elements

Output status indication	LED	4 x yellow
--------------------------	-----	------------

## Electrical connection

Connection	M12 connector; Gold-plated contacts
------------	-------------------------------------

## Wiring



## Accessories

Accessories (included)	2 lock nuts
------------------------	-------------

## Remarks

Pack quantity	[piece]	1
---------------	---------	---