

# SACC-M12FS-5QO SH DN - Data connector



1422760

<https://www.phoenixcontact.com/gb/products/1422760>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Data connector, CANopen®, DeviceNet™, 5-position, halogen-free, shielded, Socket straight M12, coding: A, Insulation displacement connection, knurl material: Zinc die-cast, nickel-plated, external cable diameter 5 mm ... 9.7 mm

## Your advantages

- Safe use in the field, thanks to a high degree of protection
- Insulation displacement connection: innovative and time-saving assembly without stripping the single wire
- Reliable signal transmission – 360° shielding in environments with electromagnetic interference

## Commercial data

|                                      |                     |
|--------------------------------------|---------------------|
| Item number                          | 1422760             |
| Packing unit                         | 1 pc                |
| Minimum order quantity               | 1 pc                |
| Sales key                            | AF2CDD              |
| Product key                          | AF2CDD              |
| Catalog page                         | Page 423 (C-2-2019) |
| GTIN                                 | 4055626312972       |
| Weight per piece (including packing) | 46.5 g              |
| Weight per piece (excluding packing) | 22.22 g             |
| Customs tariff number                | 85366990            |
| Country of origin                    | DE                  |

# SACC-M12FS-5QO SH DN - Data connector



1422760

<https://www.phoenixcontact.com/gb/products/1422760>

## Technical data

### Notes

Assembly note

**NOTE:** Observe the permissible bending radii when routing cables, since the degree of protection may be at risk if the bending forces are too high. Reduce mechanical loads upstream of the connector, e.g., by using cable ties.

### Product properties


|                      |                                 |
|----------------------|---------------------------------|
| Product type         | Circular connector (cable-side) |
| Sensor type          | CANopen®                        |
| Number of positions  | 5                               |
| No. of cable outlets | 1                               |
| Shielded             | yes                             |
| Coding               | A                               |
| Cable outlet         | straight                        |

### Insulation characteristics

|                      |    |
|----------------------|----|
| Overvoltage category | II |
| Degree of pollution  | 3  |

### Dimensions

Dimensional drawing



|                        |       |
|------------------------|-------|
| Length                 | 57 mm |
| Wrench size, union nut | 15 mm |

### External dimensions

|                  |                 |
|------------------|-----------------|
| Outside diameter | 5 mm ... 9.7 mm |
|------------------|-----------------|

### Housing

|                  |       |
|------------------|-------|
| Diameter housing | 19 mm |
|------------------|-------|

### Material specifications

|                                        |                              |
|----------------------------------------|------------------------------|
| Flammability rating according to UL 94 | V0                           |
| Seal material                          | NBR                          |
| Material of grip body                  | Zinc die-cast, nickel-plated |
| Contact material                       | CuSn                         |
| Contact surface material               | Ni/Au                        |
| Contact carrier material               | PA 6.6                       |
| Material for screw connection          | Zinc die-cast, nickel-plated |
| Standards/regulations                  | PA 6.6                       |
| Wire insulation material               | PVC / PE / PP / rubber       |

# SACC-M12FS-5QO SH DN - Data connector



1422760

<https://www.phoenixcontact.com/gb/products/1422760>

## Connection data

### Conductor connection

|                              |                                    |
|------------------------------|------------------------------------|
| Connection method            | Insulation displacement connection |
| Connection cross section     | 0.14 mm² ... 0.75 mm² (flexible)   |
|                              | 0.14 mm² ... 0.5 mm² (solid)       |
| Connection cross section AWG | 26 ... 18 (flexible)               |
|                              | 26 ... 20 (solid)                  |
| Tightening torque            | M12 knurl                          |
|                              | 5 Nm (Pressure nut)                |

### Pin assignment

|                                                           |                 |
|-----------------------------------------------------------|-----------------|
| Contact   Color (signal designation)   Contact (optional) | 1 = GY (shield) |
|                                                           | 2 = RD          |
|                                                           | 3 = BK          |
|                                                           | 4 = WH          |
|                                                           | 5 = BU          |

## Electrical properties

|                                |          |
|--------------------------------|----------|
| Rated surge voltage            | 0.8 kV   |
| Insulation resistance          | ≥ 100 MΩ |
| Nominal voltage U <sub>N</sub> | 48 V AC  |
|                                | 60 V DC  |
| Nominal current I <sub>N</sub> | 4 A      |

## Mechanical properties

### Mechanical data

|                             |       |
|-----------------------------|-------|
| Insertion/withdrawal cycles | ≥ 100 |
|-----------------------------|-------|

## Connector

### Connection 1

|                   |          |
|-------------------|----------|
| Head design       | Socket   |
| Head cable outlet | straight |
| Head thread type  | M12      |
| Coding            | A        |

## Cable/line

|                      |            |
|----------------------|------------|
| Signal type/category | CANopen®   |
|                      | DeviceNet™ |

## Environmental and real-life conditions

### Ambient conditions

|                      |      |
|----------------------|------|
| Degree of protection | IP65 |
|----------------------|------|

# SACC-M12FS-5QO SH DN - Data connector



1422760

<https://www.phoenixcontact.com/gb/products/1422760>

|                                 |                                  |
|---------------------------------|----------------------------------|
|                                 | IP67                             |
| Ambient temperature (operation) | -40 °C ... 85 °C (Plug / socket) |
| Ambient temperature (assembly)  | -5 °C ... 50 °C                  |

## Standards and regulations

### Testing

|                       |                                                                                                                                  |
|-----------------------|----------------------------------------------------------------------------------------------------------------------------------|
| Standards/regulations | PA 6.6: Fire protection in rail vehicles - requirement sets R22, R23, R24, and R26 acc. to DIN EN 45545-2 (Risk level HL1 - HL3) |
|-----------------------|----------------------------------------------------------------------------------------------------------------------------------|

### M12

|                          |                              |
|--------------------------|------------------------------|
| Standard designation     | M12 connector                |
| Standards/specifications | according to IEC 61076-2-101 |
| Standard designation     | Shock, vibration             |
| Standards/specifications | EN 50155:2001                |


# SACC-M12FS-5QO SH DN - Data connector

1422760

<https://www.phoenixcontact.com/gb/products/1422760>


## Drawings

Dimensional drawing



M12 x 1 socket, straight, shielded

Functional drawing




# SACC-M12FS-5QO SH DN - Data connector



1422760

<https://www.phoenixcontact.com/gb/products/1422760>

Schematic diagram



Pin assignment M12 socket, 5-pos., A-coded, socket side view

# SACC-M12FS-5QO SH DN - Data connector



1422760

<https://www.phoenixcontact.com/gb/products/1422760>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-12.0 | 27440116 |
| ECLASS-13.0 | 27440116 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC002635 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# SACC-M12FS-5QO SH DN - Data connector



1422760

<https://www.phoenixcontact.com/gb/products/1422760>

## Environmental product compliance

### EU RoHS

|                                         |                    |
|-----------------------------------------|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|-----------------------------------------|--------------------|

### China RoHS

|                                        |                                          |
|----------------------------------------|------------------------------------------|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|                                        | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)