

Logitech®

Stereo Headset H151

Speak clearly.

- Works with common calling applications across almost all platforms and operating systems
- Simple in-line controls
- Full stereo sound
- Noise-cancelling microphone
- Microphone can be worn left or right side

Crisp calls with stereo sound make it easy to stay in touch. The noise-cancelling microphone reduces annoying background noise so you can be heard clearly. You can wear the microphone on your left or right, and rotate it up and out of your way when you're not using it. Personalise your fit with the adjustable headband and foam ear cups. Simple in-line controls make it easy to adjust the volume and mute the microphone. It's easy to set up, too. Just plug your headset and it works with common calling applications across almost all platforms and operating systems.



Stereo Headset H151

Package specification

| | Primary pack | Master shipper carton |
|-------------------------|------------------------|-------------------------|
| Part # EMEA | 981-000589 | n/a |
| Bar code | 5099206057333 (EAN-13) | 50992060573318 (SCC-14) |
| Weight | 263 gr | 1430 gr |
| Length | 19.10 cm | 29.00 cm |
| Width | 6.99 cm | 20.60 cm |
| Height/depth | 23.97 cm | 25.60 cm |
| Volume | 3.200 dm ³ | 0.0153 m ³ |
| 1 primary pack | 1 | n/a |
| 1 intermediate pack | 0 | n/a |
| 1 master shipper carton | 4 | 1 |
| 1 pallet EURO | 448 | 112 |
| 1 container 20 ft | 7920 | 1980 |
| 1 container 40 ft | 16236 | 4059 |
| 1 container 40 ft HQ | 18040 | 4510 |

Technical Specs

- Input impedance: 22 ohms
- Sensitivity (headphone): 122 dB +/-3 dB
- Sensitivity (microphone): -44 dBV/PA +/- 2.5 dB
- Frequency response (headset): 20 Hz to 20 kHz
- Frequency response (microphone): 100 Hz to 6,500 Hz
- Cord length: 1.8 m (5.9 ft)

Package contents

- Analogue headset
- User documentation
- 2-year manufacturer's guarantee and full product support

System Requirements

- Windows® 8, Windows® 7 or Windows Vista®
- Mac OS X 10.5 or later
- Chrome OS™
- Linux Kernel 2.6+
- iOS™ or Android™
- Single 3.5 mm jack

