




Relays & Contactors > Electromechanical Relays



Relay & Contactor Type: **High Voltage Contactor**

Current Type: **DC**

Contact Arrangement: **1 Form X SPST-NO**

Contact Current Rating: **150 A**

Coil Voltage Rating: **12 VDC**

Features

Product Type Features

| | |
|------------------------|------------------------|
| Relay & Contactor Type | High Voltage Contactor |
|------------------------|------------------------|

Configuration Features

| | |
|--------------------------------------|------------------|
| Auxiliary Switch Contact Arrangement | SPST NO |
| Contact Number of Poles | 1 |
| Contact Arrangement | 1 Form X SPST-NO |

Electrical Characteristics

| | |
|---------------------------------|----------|
| Coil Resistance | 26 Ω |
| Contact Switching Voltage (Max) | 1000 VDC |
| Contact Current Rating | 150 A |
| Coil Voltage Rating | 12 VDC |

Body Features

| | |
|----------------|---------------------|
| Enclosure Type | Hermetically Sealed |
|----------------|---------------------|

Termination Features

| | |
|-----------------------------------------|----------------|
| Auxiliary Termination & Connection Type | Wire Connector |
| Main Termination & Connection Type | M5 Female |
| Coil Termination & Connection Type | Connector |

Mechanical Attachment



| | |
|--------------------|----------------|
| Torque (Main) | 30 – 40 in-lbs |
| Product Mount Type | Chassis Mount |

Dimensions

| | |
|------------------|---------------|
| Coil Wire Length | 389 mm[15 in] |
|------------------|---------------|

Operation/Application

| | |
|--------------|----|
| Current Type | DC |
|--------------|----|

Product Compliance

For compliance documentation, visit the product page on TE.com>

| | |
|-----------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| EU RoHS Directive 2011/65/EU | Compliant with Exemptions |
| EU ELV Directive 2000/53/EC | Compliant with Exemptions |
| China RoHS 2 Directive MIIT Order No 32, 2016 | Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JAN 2024 (240) SVHC > Threshold: Pb (.35% in machined component) Article Safe Usage Statements: Do not eat, drink or smoke when using this product. Wash thoroughly after handling. Recycle if possible and dispose of the article by following all applicable governmental regulations relevant to your geographic location. |
| Halogen Content | Not Yet Reviewed for halogen content |
| Solder Process Capability | Not reviewed for solder process capability |

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>


Compatible Parts



Also in the Series | Kilovac LEV100



Customers Also Bought





Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_6-1618412-9_B.3d_stp.zip

English

Customer View Model

ENG_CVM_CVM_6-1618412-9_B.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_6-1618412-9_B.3d_igs.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SD-LEV100H = CONTACTOR WITH AUX CONTACT

English