

servo motor SH3 055 0,42Nm,nokey,multi,brake, 90°conn.IP54/IP65,9k RPM

SH30551P02F2000

EAN Code: 3606485295121

Main

Range compatibility	PacDrive 3
Device short name	SH3
Product or component type	Servo motor

Complementary

Maximum mechanical speed	9000 rpm	
[Us] rated supply voltage	115480 V	
Network number of phases	Three phase	
Continuous stall current	0.73 A	
Continuous stall torque	0.42 N.m at 115480 V three phase	
Continuous power	290 W	
Peak stall torque	1.5 N.m at 115480 V three phase	
Nominal output power	100 W at 115 V single phase 210 W at 230 V single phase 400 W at 400 V three phase 440 W at 480 V three phase	
Nominal torque	0.5 N.m at 115 V single phase 0.5 N.m at 230 V single phase 0.35 N.m at 400 V three phase 0.35 N.m at 480 V three phase	
Nominal speed	2000 rpm at 115 V single phase 4000 rpm at 230 V single phase 8000 rpm at 400 V three phase 8000 rpm at 480 V three phase	
Maximum current Irms	2.9 A	
Shaft end	Smooth shaft	
Shaft diameter	9 mm	
Shaft length	20 mm	
IP degree of protection	IP54 shaft bushing without shaft seal ring: conforming to IEC 60034-5 IP65 motor: conforming to IEC 60034-5 IP65 shaft bushing: conforming to IEC 60034-5	
Encoder type	Absolute multiturn SinCos Hiperface	
Speed feedback resolution	128 periods	
Holding brake	With	
Holding torque	0.8 N.m	
Mounting support	International standard flange	
Motor flange size	55 mm	

Electrical connection	Straight connector	
Torque constant	0.58 N.m/A at 120 °C	
Back emf constant	40 V/krpm at 20 °C	
Number of motor poles	3.0	
Rotor inertia	0.08 kg.cm ²	
Stator resistance	41.8 Ohm	
Stator inductance	37.13 mH	
Maximum radial force Fr	340 N at 1000 rpm 270 N at 2000 rpm 240 N at 3000 rpm 220 N at 4000 rpm 200 N at 5000 rpm 190 N at 6000 rpm 180 N at 7000 rpm 170 N at 8000 rpm	
Maximum axial force Fa	40 N	
type of cooling	Natural convection	
Length	159 mm	
Centring collar diameter	40 mm	
centring collar depth	2 mm	
Number of mounting holes	4	
Mounting holes diameter	5.5 mm	
Circle diameter of the mounting holes	63 mm	
Net weight	1.3 kg	
Sizing reference	SH30551P	
Network number of phases	3	
Temperature copper hot	130 °C	
compatible drive output current 3s peak 2	6 A	
Electrical connection	rotatable right angled connector	

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	11.5 cm
Package 1 Width	19.0 cm
Package 1 Length	39.5 cm
Package 1 Weight	1.837 kg
Unit Type of Package 2	S04
Number of Units in Package 2	3
Package 2 Height	30 cm
Package 2 Width	40 cm
Package 2 Length	60 cm
Package 2 Weight	6.351 kg

Logistical informations

Country of origin

DE

Contractual warranty

Warranty

1 Jul 2025

18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

☑ Environmental footprint		
Carbon footprint (kg.eq.CO2 per CR, Total Life cycle)	961	
Environmental Disclosure	Product Environmental Profile	

Use Better

Materials and Substances	
Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ead0850d-370a-47c5-8cf7-1d93c2c974a4
REACh Regulation	REACh Declaration
PVC free	Yes

Use Again

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No
WEEE	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins