

Features

- 94mm cubic-design LED steady/flashing beacon with built-in buzzer indicator
- Steady and flashing light can be switched externally
- Beacon with good frontal and lateral signalling effect
- Beacon with 30cd luminous intensity
- Buzzer indicator provides 80dB (A) sound pressure
- High degree of protection IP65
- Optional mounting type using metal bracket
- 24V AC/DC supply voltage

RS PRO Beacons

Auer Signal: 0694319



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

- 94mm cubic-design LED steady/flashing beacon with built-in buzzer indicator.
- Steady and flashing light can be switched externally.
- 16 LED light sources with a service life light source of >50,000 hours
- Ideal frontal and lateral signalling effect
- Buzzer max. 80 dB (A) sound pressure with a tone frequency of 3.5kHz
- 2 tones available that can be switched externally, steady tone or pulsing tone.
- Beacon with good frontal/lateral signalling effect
- Can be mounted directly on walls horizontally or vertically.
- Offers a high degree of protection (IP65) with a IK07 impact resistant rating.
- For industrial, plant construction, logistics and general applications
- Full mounting accessory package available

General Specifications

Lens	Polycarbonate
Nominal flash rate	1.4 Hz
Bulb Type	LED
Light Effect	Strobe/Flashing
Lens Colour	Red. Polycarbonate, ribbed inside
Fitting	4 bolt
Flash Pattern	Single
Housing Colour	Red.
Lamp Include	Yes
Multifunction	Yes
Number of flash patterns	2
Number of LED	16
Special Features	Buzzer volume: 80db 2 Tones: Steady tone or Pulsing tone Tone frequency: 3.5kHz
Protection	Against water & dust, vibration (IK07)

Electrical Specifications

Supply Voltage	24V AC/DC
Light Output	30 Cd
Current Type	AC/DC
Current Consumption	140mA

Mechanical Specifications

Dimensions	94mm (w) x 99mm (d) x 94mm (h)
Base Diameter	94mm
Base Length	99mm
Base Width	94mm
Mounting Style	Screw Mount
Weight	300g

Operation Environment Specifications

Maximum Temperature	+60°C
Minimum Temperature	-30°C

Protection Category

IP Rating	IP65
------------------	------

Approvals

Compliance/Certifications	CE / UL
Declarations	RoHS Compliant / REACH
Standards Met	Yes
Hazardous Area Certification	N/A

