

Datasheet

HSS Jobber Drill Bit



Features & Benefits

- Titanium Nitride Coated (TiN)
- Longer shaft length
- Right angle cutting tip
- 118° cutting angle
- Available in sizes from 0.25 – 20mm
- Suitable for metals, woods, plastics

Standards

DIN 338; BS 328-ISO 235/1



ENGLISH

Stock Number	Diameter (mm)	Cutting Length (mm)	Overall Length (mm)
213-887	1.0	12	34
213-900	1.1	14	36
213-310	1.2	16	38
213-893	1.3	16	38
213-376	1.4	18	40
213-871	1.5	18	40
213-859	1.6	20	43
213-433	1.7	20	43
213-865	1.8	22	46
213-972	1.9	22	46
213-916	2.0	24	49
213-966	2.1	24	49
213-950	2.2	27	53
213-944	2.3	27	53
213-938	2.4	30	57
213-922	2.5	30	57
213-843	2.6	30	57
213-764	2.7	33	61
213-758	2.8	33	61
213-427	2.9	33	61
213-411	3.0	33	61
213-382	3.1	36	65
213-405	3.2	36	65
213-398	3.3	36	65
213-742	3.4	39	70
213-304	3.5	39	70
213-720	3.6	39	70
213-714	3.7	39	70
213-736	3.8	43	75
213-837	3.9	43	75
213-821	4.0	43	75
213-770	4.1	43	75
213-809	4.2	43	75
213-815	4.3	47	80
213-792	4.4	47	80
214-177	4.5	47	80
213-786	4.6	47	80
214-161	4.7	47	80



ENGLISH

Stock Number	Diameter (mm)	Cutting Length (mm)	Overall Length (mm)
213-225	4.8	52	86
213-219	4.9	52	86
213-203	5.0	52	86
213-196	5.1	52	86
213-180	5.2	52	86
213-174	5.3	52	86
213-231	5.4	57	93
213-281	5.5	57	93
213-297	5.6	57	93
213-275	5.7	57	93
213-269	5.8	57	93
213-253	5.9	57	93
213-635	6.0	57	93
213-247	6.1	63	101
214-155	6.2	63	101
213-629	6.3	63	101
214-149	6.4	63	101
213-613	6.5	63	101
214-133	6.6	63	101
213-607	6.8	69	109
214-183	6.9	69	109
214-240	7.0	69	109
214-212	7.2	69	109
214-199	7.5	69	109
214-010	7.9	75	117
214-004	8.0	75	117
213-691	8.5	75	117
214-048	9.0	81	125
214-076	9.5	81	125
213-499	10.0	87	133
214-054	10.2	87	133
213-326	10.5	87	133
213-461	11.0	94	142
213-506	11.5	94	142
213-534	12.0	101	151
213-540	13.0	101	151