





- | | | | | | | |
|---|---------|-------------------|------------------|----|---------------------|-------------|
| | 7 | 101.19
[3.984] | 99.06
[3.900] | 39 | 80 | 9-146258-0 |
| 8 | 7 | 98.65
[3.884] | 96.52
[3.800] | 38 | 78 | 8-146258-9 |
| 8 | 7 | 96.11
[3.784] | 93.98
[3.700] | 37 | 76 | 8-146258-8 |
| 8 | 7 | 93.57
[3.684] | 91.44
[3.600] | 36 | 74 | 8-146258-7 |
| 8 | 7 | 91.03
[3.584] | 88.90
[3.500] | 35 | 72 | 8-146258-6 |
| 8 | 7 | 88.49
[3.484] | 86.36
[3.400] | 34 | 70 | 8-146258-5 |
| 8 | 7 | 85.95
[3.384] | 83.82
[3.300] | 33 | 68 | 8-146258-4 |
| 8 | 7 | 83.41
[3.284] | 81.28
[3.200] | 32 | 66 | 8-146258-3 |
| 8 | 7 | 80.87
[3.184] | 78.74
[3.100] | 31 | 64 | 8-146258-2 |
| 8 | 7 | 78.33
[3.084] | 76.20
[3.000] | 30 | 62 | 8-146258-1 |
| 8 | 7 | 75.79
[2.984] | 73.66
[2.900] | 29 | 60 | 8-146258-0 |
| 8 | 7 | 73.25
[2.884] | 71.12
[2.800] | 28 | 58 | 7-146258-9 |
| 8 | 7 | 70.71
[2.784] | 68.58
[2.700] | 27 | 56 | 7-146258-8 |
| 8 | 7 | 68.17
[2.684] | 66.04
[2.600] | 26 | 54 | 7-146258-7 |
| 8 | 7 | 65.63
[2.584] | 63.5
[2.500] | 25 | 52 | 7-146258-6 |
| 8 | 7 | 63.09
[2.484] | 60.96
[2.400] | 24 | 50 | 7-146258-5 |
| 8 | 7 | 60.55
[2.384] | 58.42
[2.300] | 23 | 48 | 7-146258-4 |
| 8 | 7 | 58.01
[2.284] | 55.88
[2.200] | 22 | 46 | 7-146258-3 |
| 8 | 7 | 55.47
[2.184] | 53.34
[2.100] | 21 | 44 | 7-146258-2 |
| 8 | 7 | 52.93
[2.084] | 50.80
[2.000] | 20 | 42 | 7-146258-1 |
| 8 | 7 | 50.39
[1.984] | 48.26
[1.900] | 19 | 40 | 7-146258-0 |
| 8 | 7 | 47.85
[1.884] | 45.72
[1.800] | 18 | 38 | 6-146258-9 |
| 8 | 7 | 45.31
[1.784] | 43.18
[1.700] | 17 | 36 | 6-146258-8 |
| 8 | 7 | 42.77
[1.684] | 40.64
[1.600] | 16 | 34 | 6-146258-7 |
| 8 | 7 | 40.23
[1.584] | 38.10
[1.500] | 15 | 32 | 6-146258-6 |
| 8 | 7 | 37.69
[1.484] | 35.56
[1.400] | 14 | 30 | 6-146258-5 |
| 8 | 7 | 35.15
[1.384] | 33.02
[1.300] | 13 | 28 | 6-146258-4 |
| 8 | 7 | 32.61
[1.284] | 30.48
[1.200] | 12 | 26 | 6-146258-3 |
| 8 | 7 | 30.07
[1.184] | 27.94
[1.100] | 11 | 24 | 6-146258-2 |
| 8 | 7 | 27.53
[1.084] | 25.40
[1.000] | 10 | 22 | 6-146258-1 |
| 8 | 7 | 24.99
[.984] | 22.86
[.900] | 9 | 20 | 6-146258-0 |
| | 7 | 22.45
[.884] | 20.32
[.800] | 8 | 18 | 5-146258-9 |
| | 7 | 19.91
[.784] | 17.78
[.700] | 7 | 16 | 5-146258-8 |
| | 7 | 17.37
[.684] | 15.24
[.600] | 6 | 14 | 5-146258-7 |
| | 7 | 14.83
[.584] | 12.70
[.500] | 5 | 12 | 5-146258-6 |
| | 7 | 12.29
[.484] | 10.16
[.400] | 4 | 10 | 5-146258-5 |
| | 7 | 9.75
[.384] | 7.62
[.300] | 3 | 8 | 5-146258-4 |
| | 7 | 7.21
[.284] | 5.08
[.200] | 2 | 6 | 5-146258-3 |
| | 7 | 4.67
[.184] | 2.54
[.100] | 1 | 4 | 5-146258-2 |
| | 7 | - | - | 0 | 2 | 5-146258-1 |
| | PLATING | C | B | A | NO. OF
POSITIONS | PART NUMBER |



THIS DRAWING IS A CONTROLLED DOCUMENT.						DWG	RE	BROWN	19JAN05	 TE Connectivity	
DIMENSIONS: mm [INCHES] 											