

609A - Variable pitch holesaws



Description:

- Variable pitch holesaws 4 to 6 mm.
- Softer cut and reduced vibration.
- Cutting depth 34 mm.
- Chuck and drill for holesaws 19 to 29 mm 609A.M1.
- Chuck and drill for holesaws 35 to 68 mm 609A.M2.
- Set of 2 spare bits + chuck screws: 609.M-ACC.

	Diameter [mm]	Length L [mm]	Weight [g]
609A.65	65.0	45.0	200.0